

## SF 0/21 MC NE BL V2


Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

## Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

## General ordering data

|            |   |
|------------|---|
| Version    | SlimFix, Conductor and cable markers, 1.2 - 1.6 mm, 21 x 3.2 mm, blue |
| Order No.  | <a href="#">1918510000</a>  |
| Type       | SF 0/21 MC NE BL V2   |
| GTIN (EAN) | 4032248553938   |
| Qty.       | 400 items   |

SF 0/21 MC NE BL V2

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 3.2 mm | Depth (inches)  | 0.126 inch  |
| Height     | 21 mm  | Height (inches) | 0.8268 inch |
| Width      | 3.2 mm | Width (inches)  | 0.126 inch  |
| Net weight | 0.3 g  |                 |             |

Temperatures

Operating temperature range -40...100 °C

Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.002 kg CO2 eq. |  |

General data

|                                      |   |           |  |
|--------------------------------------|---|-----------|--|
| Type of printing                     | neutral   |           |  |
| Width                                | 3.2 mm  |           |  |
| UL 94 flammability rating            | V-2   |           |  |
| Operating temperature range, max.    | 100 °C  |           |  |
| Operating temperature range, min.    | -40 °C  |           |  |
| Colour                               | blue  |           |  |
| Halogen                              | No  |           |  |
| Basic material                       | Polyamide 66  |           |  |
| Number of markers per packaging unit | Form of supply  | MultiCard |  |
| Size of labelling field              | 21 x 3.2 mm   |           |  |
| Recommended industries               | Transportation, Machinery   |           |  |
| compatible printer                   | <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a> |           |  |
| Number of markers per combination    | 1 MultiCard = Conductor and cable markers   |           |  |
| Operating temperature range          | -40...100 °C  |           |  |

Conductor and cable markers

|                                  |                            |                               |                     |
|----------------------------------|----------------------------|-------------------------------|---------------------|
| Halogen                          | No                         | Conductor cross-section, max. | 0.5 mm <sup>2</sup> |
| Conductor cross-section, min.    | 0.25 mm <sup>2</sup>       | Conductor O.D., max.          | 1.6 mm              |
| Conductor O.D., min.             | 1.2 mm                     | Conductor O.D.                | 1.2 - 1.6 mm        |
| Cross-section for connected wire | 0.25 - 0.5 mm <sup>2</sup> |                               |                     |

Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

