

SF 6/21 MC NE GE V2


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm, yellow
Order No.	1919170000
Type	SF 6/21 MC NE GE V2
GTIN (EAN)	403224855567
Qty.	160 items

SF 6/21 MC NE GE V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	8.5 mm	Depth (inches)	0.3346 inch
Height	21 mm	Height (inches)	0.8268 inch
Width	8.4 mm	Width (inches)	0.3307 inch
Net weight	0.63 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.006 kg CO2 eq.	

General data

Type of printing	neutral		
Width	8.4 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	yellow		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	21 x 8.4 mm		
Recommended industries	Transportation, Machinery		
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-40...100 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	10 mm ²	Conductor O.D., max.	7.8 mm
Conductor O.D., min.	5.8 mm	Conductor O.D.	5.8 - 7.8 mm
Cross-section for connected wire	10 - 16 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

