

SF 4/12 MC NE BL V2


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 3.6 - 6 mm, 12 x 5.7 mm, blue
Order No.	1919590000
Type	SF 4/12 MC NE BL V2
GTIN (EAN)	4032248556014
Qty.	128 items

SF 4/12 MC NE BL V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.2402 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	5.7 mm	Width (inches)	0.2244 inch
Net weight	0.65 g		

Temperatures

Operating temperature range -40...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.004 kg CO2 eq.	

General data

Material colour according to resistance code	6		
Type of printing	neutral		
Width	5.7 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	blue		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	12 x 5.7 mm		
Recommended industries compatible printer	Transportation, Machinery PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-40...100 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	2.5 mm ²	Conductor O.D., max.	6 mm
Conductor O.D., min.	3.6 mm	Conductor O.D.	3.6 - 6 mm
Cross-section for connected wire	2.5 - 4 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

