

**SAISGT-P-12A-6/8-M12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The solder connection provides high contact density on a small area. With this technology the stripped conductor is soldered to the contacts, producing good electrical conductivity.

**General ordering data**

|            |                                 |
|------------|---------------------------------|
| Version    | Field attachable connector, M12 |
| Order No.  | <a href="#">1924950000</a>      |
| Type       | SAISGT-P-12A-6/8-M12            |
| GTIN (EAN) | 4032248565757                   |
| Qty.       | 1 items                         |

## SAISGT-P-12A-6/8-M12

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E307231                    |

## Dimensions and weights

|            |      |
|------------|------|
| Net weight | 19 g |
|------------|------|

## Environmental Product Compliance

|                                      |  |
|--------------------------------------|--|
| RoHS Compliance Status               | Compliant with exemption                       |
| RoHS Exemption (if applicable/known) | 6c   |
| REACH SVHC                           | Lead 7439-92-1, Imidazolidine-2-thione 96-45-7 |
| SCIP                                 | bcee35cf-c0f5-43d2-8daf-65ab0d08641a           |

## Technical data customisable plug-in connectors

|                               |                      |                               |                      |
|-------------------------------|----------------------|-------------------------------|----------------------|
| Number of poles               | 12                   | Coding                        | A-coded              |
| Contact surface               | Gold-plated          | Type of connection            | Solder connection    |
| Housing main material         | PA                   | Insulation resistance         | 108 Ω                |
| Cable diameter, max.          | 8 mm                 | Cable diameter, min.          | 6 mm                 |
| Conductor cross-section, max. | 0.25 mm <sup>2</sup> | Conductor cross-section, min. | 0.14 mm <sup>2</sup> |
| Nominal voltage               | 30 V                 | Nominal current               | 1.5 A                |
| Protection degree             | IP67                 | Plugging cycles               | ≥ 100                |
| Pollution severity            | 3                    | Gender of contact             | Male                 |
| Shield connection             | No                   | Threaded ring material        | Diecast zinc         |
| Temperature range of housing  | -40 ... +85 °C       |                               |                      |

## General Info

|                   |                   |                       |             |
|-------------------|-------------------|-----------------------|-------------|
| Number of poles   | 12                | Connection 1          | M12         |
| Connection 2      | Solder connection | Housing main material | PA          |
| Connection thread | M12               | Contact surface       | Gold-plated |
| Protection degree | IP67              | Plugging cycles       | ≥ 100       |

## Standards

|                    |                 |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-101 |
|--------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002635    | ETIM 9.0    | EC002635    |
| ETIM 10.0   | EC002635    | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 |             |             |

**Pole scheme**

