

SAIL-M12BW-4-50V

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Version	Sensor/actuator line, One end without connector, M12, Number of poles : 4, 50 m, Socket, angled, Shielded: No, LED: No, Sheath material: PVC, Halogen: Yes
Order No.	1925645000
Type	SAIL-M12BW-4-50V
GTIN (EAN)	4050118427493
Qty.	1 items

SAIL-M12BW-4-50V

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



RoHS Conform

Dimensions and weights

Net weight 2063 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP 1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Technical specifications for cable

Cable length	50 m
Suitable for cable carriers	No
Shielded	No
Insulation	PVC
Configurable cable length	No
Irradiation crosslinked	No
Colour coding	brown, white, blue, black
Temperature range, stationary	-30...80 °C
Temperature range, moving	-5...80 °C
Outside diameter	5.3 mm ± 0.2 mm

Sheathing colour	black
Core cross-section	0.34 mm ²
Halogen	Yes
Sheath material	PVC
Outer cladding in accordance with UL AWM style	2464 (80 °C / 300 V)
Welding spark resistance	No
Torsion resistance	0 °/m
Resistant to welding beads	No
Number of poles	4

General technical data

Coding	A-coded
Contact surface	Gold-plated
Version	Socket, angled
Insulation resistance	108 Ω
Nominal current	4 A
Plugging cycles	≥ 100
jumpered	No
Temperature range of housing	-25...+85 °C

Connection thread	M12
LED	No
Housing main material	PUR
Nominal voltage	250 V
Protection degree	IP67, IP68, when screwed in, IP65, IP66
Pollution severity	3
Threaded ring material	Diecast zinc
Tightening torque	M12: 0.8 - 1.2 Nm

Electrical properties

Insulation resistance	108 Ω
Nominal voltage	250 V

General standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Standards	
-----------	--

Connector standard	IEC 61076-2-101
--------------------	-----------------

SAIL-M12BW-4-50V

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

Plug left M12, A-coded, IP69,
female contact, angled
90°, Plastic, unshielded

Plug, right

Plug right free conductor end




Classifications

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		

SAIL-M12BW-4-50V

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Dimensioned drawing****Pole scheme****Wiring diagram****The ideal tool: Screwty ® with torque function**

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

SAIL-M12BW-4-50V

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings
