

TS15 147 KLIPPON POK3 CSS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
-
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Rail, TS 15, Width: 147 mm, without slot, Steel, galvanized, chromium-plated
Order No.	1928080000
Type	TS15 147 KLIPPON POK3 CSS
GTIN (EAN)	4032248577064
Qty.	1 items

TS15 147 KLIPPON POK3 CSS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	147 mm	Width (inches)	5.7874 inch
Net weight	29 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	1 mm	Installation advice	Direct mounting
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated
Basic material	Steel	Integral fixing	Screwed
Stamp dimensions	4.5 x 20 mm		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02
ECLASS 13.0	27-40-06-02	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		