


WTQ 6/1 EN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|---|
| Version | Measuring transformer disconnect terminal, Screw connection, 500, 41, 2 |
| Order No. | 1934790000 |
| Type | WTQ 6/1 EN |
| GTIN (EAN) | 4032248592142 |
| Qty. | 50 items |

Technical data

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

| | |
|-----------------------|----------------------------|
| UL File Number Search | UL Website |
|-----------------------|----------------------------|

| | |
|----------------------|--------|
| Certificate No. (UR) | E60693 |
|----------------------|--------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 47.5 mm | Depth (inches) | 1.8701 inch |
| Height | 65 mm | Height (inches) | 2.5591 inch |
| Width | 7.9 mm | Width (inches) | 0.311 inch |
| Net weight | 20.93 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 0eb7d846-d0a1-43e5-93a4-d7c6856c4cda |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Basic material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-------------------------------------|--|-------------------------------|--------------|
| Version | Screw connection, Spacer, for plug-in cross-connector, One end without connector | End cover plate required | Yes |
| Number of potentials | 1 | Number of levels | 1 |
| Number of clamping points per level | 2 | Number of potentials per tier | 1 |
| PE connection | No | Mounting rail | TS 35, TS 32 |
| N-function | No | PE function | No |
| PEN function | No | | |

Additional technical data

| | | | |
|--------------------------|--------|-----------------------------|---------|
| Open sides | closed | Number of similar terminals | 1 |
| Explosion-tested version | No | Type of mounting | Snap-on |

CSA rating data

| | | | |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 8 AWG | Voltage size C (CSA) | 300 V |
| Current size C (CSA) | 45 A | Certificate No. (CSA) | 200039-1057876 |
| Voltage size B (CSA) | 300 V | Current size B (CSA) | 45 A |
| Wire cross section min. (CSA) | 20 AWG | | |

Technical data

Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|---------------------|
| Gauge to IEC 60947-1 | A5 | Wire connection cross section AWG, max. | AWG 8 |
| Connection direction | on side | Stripping length | 12 mm |
| Type of connection | Screw connection | Number of connections | 2 |
| Clamping range, max. | 10 mm ² | Clamping range, min. | 0.5 mm ² |
| Clamping screw | M 3.5 | Blade size | 0.8 x 4.0 mm |
| Wire connection cross section AWG, min. | AWG 20 | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross section, finely stranded, max. | 10 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Connection cross-section, stranded, max. | 10 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² | Torque level with DMS electric screwdriver | 3 |
| Wire connection cross-section, solid core, max. | 10 mm ² | Wire connection cross-section, solid core, min. | 0.5 mm ² |

Dimensions

TS 35 offset 34.5 mm

General

| | | | |
|---|--------------|---|--------|
| Wire connection cross section AWG, max. | AWG 8 | Wire connection cross section AWG, min. | AWG 20 |
| Mounting rail | TS 35, TS 32 | | |

Rating data


| | | | |
|---------------------------------|-------------------|--|---------|
| Rated cross-section | 6 mm ² | Rated voltage | 500 V |
| Rated DC voltage | 500 V | Nominal current | 41 A |
| Current at maximum wires | 57 A | Volume resistance according to IEC 60947-7-x | 0.78 mΩ |
| Rated impulse withstand voltage | 6 kV | Power loss in accordance with IEC 60947-7-x | 1.31 W |
| Pollution severity | 3 | | |

UL rating data

| | | | |
|---|--------|---|--------|
| Voltage size B (UR) | 300 V | Current size B (UR) | 45 A |
| Conductor size Factory wiring max. (UR) | 8 AWG | Current size C (UR) | 45 A |
| Voltage size C (UR) | 300 V | Conductor size Factory wiring min. (UR) | 20 AWG |
| Certificate No. (UR) | E60693 | Conductor size Field wiring min. (UR) | 20 AWG |
| Conductor size Field wiring max. (UR) | 8 AWG | | |

Technical data**Classifications**

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 7.0 | EC000902 | ETIM 8.0 | EC000902 |
| ETIM 9.0 | EC000902 | ETIM 10.0 | EC000902 |
| ECLASS 11.0 | 27-14-11-26 | ECLASS 12.0 | 27-14-11-26 |
| ECLASS 13.0 | 27-25-01-09 | ECLASS 14.0 | 27-25-01-09 |
| ECLASS 15.0 | 27-25-01-09 | | |



Accessories

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WQV 6/2 | Version |
| Order No. | 1052360000 | Cross-connector (terminal), when screwed in, yellow, 57 A, Number of |
| GTIN (EAN) | 4008190075866 | poles: 2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 7.6 mm |
| Qty. | 50 ST | |
| Type | WQV 6/3 | Version |
| Order No. | 1054760000 | Cross-connector (terminal), when screwed in, yellow, 57 A, Number of |
| GTIN (EAN) | 4008190174163 | poles: 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 7.6 mm |
| Qty. | 50 ST | |
| Type | WQV 6/4 | Version |
| Order No. | 1054860000 | Cross-connector (terminal), when screwed in, yellow, 57 A, Number of |
| GTIN (EAN) | 4008190180799 | poles: 4, Pitch in mm (P): 8.00, Insulated: Yes, Width: 7.6 mm |
| Qty. | 50 ST | |
| Type | WQV 6/10 | Version |
| Order No. | 1052260000 | Cross-connector (terminal), when screwed in, yellow, 57 A, Number of |
| GTIN (EAN) | 4008190153977 | poles: 10, Pitch in mm (P): 8.00, Insulated: Yes, Width: 7.6 mm |
| Qty. | 20 ST | |

Accessorie



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WAP WTL6/1 EN | Version |
| Order No. | 1957710000 | End plate for terminals, dark beige, Height: 65 mm, Width: 1.5 mm, |
| GTIN (EAN) | 4032248654024 | V-0, Wemid, Snap-on: Yes |
| Qty. | 20 ST | |

WTQ 6/1 EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

End plates and partition plates



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WTW WTL6/1 DB | Version |
| Order No. | 1068400000 | Partition plate (terminal), dark beige, Height: 65 mm, Width: 1.5 mm, |
| GTIN (EAN) | 4008190091996 | V-0, Wemid |
| Qty. | 20 ST | |

Accessorie



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WKB 1/2 | Version |
| Order No. | 1604280000 | Cross-connector (terminal), when screwed in, orange, 41 A, Number |
| GTIN (EAN) | 4008190165338 | of poles: 2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 14.1 mm |
| Qty. | 50 ST | |

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WKB 1/3 | Version |
| Order No. | 1604300000 | Cross-connector (terminal), when screwed in, orange, 41 A, Number |
| GTIN (EAN) | 4008190010225 | of poles: 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 22 mm |
| Qty. | 50 ST | |

WTQ 6/1 EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | WKB 1/4 | Version |
| Order No. | 1604320000 | Cross-connector (terminal), when screwed in, orange, 41 A, Number |
| GTIN (EAN) | 4008190023713 | of poles: 4, Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm |
| Qty. | 50 ST | |

Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | STB 21.6/45 GE | Version |
| Order No. | 1936240000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248605972 | |
| Qty. | 50 ST | |

Accessorie



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | STB 21.6/45 BL | Version |
| Order No. | 1936290000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248606023 | |
| Qty. | 50 ST | |
| Type | STB 21.6/45 DB | Version |
| Order No. | 1938790000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248612840 | |
| Qty. | 50 ST | |

WTQ 6/1 EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | STB 21.6/45 GN | Version |
| Order No. | 1936250000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248605989 | |
| Qty. | 50 ST | |

Accessorie



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | STB 21.6/45 GR | Version |
| Order No. | 1936280000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248606016 | |
| Qty. | 50 ST | |
| Type | STB 21.6/45 RT | Version |
| Order No. | 1936300000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248606030 | |
| Qty. | 50 ST | |
| Type | STB 21.6/45 SW | Version |
| Order No. | 1936270000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248606009 | |
| Qty. | 50 ST | |
| Type | STB 21.6/45 VI | Version |
| Order No. | 1936260000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 |
| GTIN (EAN) | 4032248605996 | |
| Qty. | 50 ST | |

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | DEK 5/8 MC NE WS | Version |
| Order No. | 1856740000 | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248400850 | Weidmueller, white |
| Qty. | 800 ST | |
| Type | WS 12/8 PLUS MC NE WS | Version |
| Order No. | 1906000000 | WS, Terminal marker, 12 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, |
| GTIN (EAN) | 4032248528158 | white |
| Qty. | 420 ST | |

ZGB pivotable group tag holder



The ZGB 15 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 15.

The ZGB 30 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 7.


Inlay tags and protective strips can be found under "Accessories".

General ordering data

| | | |
|------------|----------------------------|---|
| Type | ZGB 15 | Version |
| Order No. | 1636530000 | Terminal markers, Terminal marker, 15 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190297053 | Weidmueller, white |
| Qty. | 20 ST | |
| Type | ZGB 30 | Version |
| Order No. | 1611930000 | Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190002251 | Weidmueller, white |
| Qty. | 20 ST | |

Accessories

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

| | | |
|------------|----------------------------|----------------------------|
| Type | BZT 1 WS 10/5 | Version |
| Order No. | 1805490000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 ST | |
| Type | BZT 1 ZA WS 10/5 | Version |
| Order No. | 1805520000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248 | |
| Qty. | 100 ST | |

DEK 5/8



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | |
|------------|----------------------------|--|
| Type | DEK 5/8 MM WS | Version |
| Order No. | 2007130000 | Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392012 | |
| Qty. | 500 ST | |

Accessories

Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | STB 36.8/IH/BL WTL6/1 | Version |
| Order No. | 1847790000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4032248379149 | |
| Qty. | 50 ST | |
| Type | STB 36.8/IH/GN WTL6/1 | Version |
| Order No. | 1847770000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4032248379163 | |
| Qty. | 50 ST | |
| Type | STB 36.8/IH/RT WTL6/1 | Version |
| Order No. | 1312540000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4050118180992 | |
| Qty. | 50 ST | |
| Type | STB 36.8/IH/SW WTL6/1 | Version |
| Order No. | 1312550000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4050118181210 | |
| Qty. | 50 ST | |