


**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Accessories, Cross-connection slider
Order No.	<a href="#">1936190000</a>
Type	WKB 2/2
GTIN (EAN)	4032248605927
Qty.	50 items

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	16.1 mm	Depth (inches)	0.6339 inch
Height	9.41 mm	Height (inches)	0.3705 inch
Width	14.1 mm	Width (inches)	0.5551 inch
Net weight	1.67 g		

## Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Polyamide 66	Colour	orange
UL 94 flammability rating	V-2		

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

## Dimensions

Pitch in mm (P)	7.90 mm
-----------------	---------

## General

Number of poles	2	Installation advice	Direct mounting
Operating temperature range, max.	100 °C		

## Rating data

Rated voltage	400 V	Nominal current	41 A
---------------	-------	-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		