

STB 21.6/45 GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | |
|------------|--|
| Version | Socket (terminal), Plug-in depth: 11.1 mm, 0.00 mm, Depth: 45 mm |
| Order No. | 1936280000 |
| Type | STB 21.6/45 GR |
| GTIN (EAN) | 4032248606016 |
| Qty. | 50 items |

STB 21.6/45 GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 45 mm | Depth (inches) | 1.7716 inch |
| Height | 6.1 mm | Height (inches) | 0.2402 inch |
| Width | 6.1 mm | Width (inches) | 0.2402 inch |
| Net weight | 3.31 g | | |

Temperatures

| | | | |
|----------------------------------|---------------|----------------------------------|--------|
| Ambient temperature | -5 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | dce63e23-eea1-4eaa-9071-1c98fc8fa2ea |

Material data

| | | | |
|---------------------------|-------|--------|------|
| Basic material | Wemid | Colour | grey |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|------------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Type of mounting | when screwed in | | |

Dimensions

| | | | |
|-------------------------------------|---------|---------------|---------|
| Metric size of the thread, external | 0.00 mm | Plug-in depth | 11.1 mm |
| TS 35 offset | 45.5 mm | | |

General

| | | | |
|---------------------|-----------------|-----------------------------------|--------|
| Installation advice | Direct mounting | Operating temperature range, max. | 100 °C |
|---------------------|-----------------|-----------------------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |