BV/SV 7.62HP/02 ZE GR



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







For frequent load changes: the "trailer coupling" for plugin connectors.

The strain relief can do more than just relieve the strain on conductors:

Simply clip onto the plug and

- bundle conductors
- guide cables
- use as a connection and disconnection aid

No damage to the connecting points, clear, tidy wiring and easy to handle.

User advantages: permanent heavy-duty connections for harsh industrial environments and convenient operation ensure improved system availability.

General ordering data

Version	PCB plug-in connector, Accessories, Strain relief, Light Grey, Number of poles: 2		
Order No.	<u>1937550000</u>		
Туре	BV/SV 7.62HP/02 ZE GR		
GTIN (EAN)	4032248608836		
Qty.	50 items		
Product data			
Packaging	Вох		



BV/SV 7.62HP/02 ZE GR



Weidmüller Interface GmbH & Co. KG

27-46-04-02

27-46-04-02

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals				
ROHS	Conform			
Dimensions and weights	Comorni			
Dimensions and weights				
Net weight	2.38 g			
Environmental Product Comp	oliance		'	
RoHS Compliance Status	Compliant without ex	vemntion		
REACH SVHC	No SVHC above 0.1 wt%			
Material data				
Insulating material	PA	Colour	Light Grey	
Colour chart (similar)	RAL 7035	Moisture Level (MSL)	Light Giby	
Contact material	Cu-alloy	Storage temperature, min.	-40 °C	
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C	
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C	
Temperature range, installation, max.	100 °C			
Rated data acc. to IEC				
tested acc. to standard	IEC 60664-1, IEC 61984			
Packing				
Packaging	Box	VPE length	127.00 mm	
VPE width	119.00 mm	VPE height	50.00 mm	
Important note			'	
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the product can be evaluated on request.			
Notes	 Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months 			
Classifications				
	= 000006=			
ETIM 6.0	EC002943	ETIM 7.0	EC002943	
ETIM 8.0	EC002943	ETIM 9.0	EC002943	
ETIM 10.0	EC002943	ECLASS 9.0	27-44-04-92	
ECLASS 9.1	27-44-04-92	ECLASS 10.0	27-44-04-92	

ECLASS 11.0

ECLASS 13.0

ECLASS 15.0

Catalogue status / Drawings 2

ECLASS 12.0

ECLASS 14.0

27-46-04-02

27-46-04-02

27-46-04-02