

SAI-AU M12 SB 4PT100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The trend from IP 20 to IP 67, or rather from machines with cabinets to ones without, reaches its zenith in the IP 67 I/O slaves. In these Plug & Play solutions, the connection of individual conductors is avoided completely. This results in a substantial time-saving and eliminates mistakes in the connection of individual conductors. Today, IP 67 bus modules represent the most modern solution for the connection of sensors and actuators with the best cost-saving potential.

General ordering data

| | |
|------------|----------------------------|
| Version | SAI Active, Subbus |
| Order No. | 1938710000 |
| Type | SAI-AU M12 SB 4PT100 |
| GTIN (EAN) | 4032248612697 |
| Qty. | 1 items |

SAI-AU M12 SB 4PT100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Height | 32 mm | Height (inches) | 1.2598 inch |
| Width | 30 mm | Width (inches) | 1.1811 inch |
| Net weight | 246.4 g | | |

Temperatures

| | | |
|---------------------|-----------------------|--------------|
| Storage temperature | Operating temperature | 0 °C...60 °C |
|---------------------|-----------------------|--------------|

Environmental Product Compliance

| | |
|--------------------------------------|--|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl |
| REACH SVHC | Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | 30ca4bfe-b33c-43ed-b218-3746bc09f6a6 |

Connections

| | | | |
|-------------------------------|--------------------------------|--------------------------------|-------------------------------|
| Connection to Subbus (SUB-IN) | 1 x M8 plug 4-pole, A-coded | Connection to Subbus (SUB-OUT) | 1 x M8 female 4-pole, A-coded |
| I/O connections | 4 x M12 female, 5-pole A-coded | | |

Digital inputs

| | |
|----------------------|-----|
| Diagnosis indication | red |
|----------------------|-----|

Digital outputs

| | |
|----------------------|-----|
| Diagnosis indication | red |
|----------------------|-----|

General data

| | | | |
|---------------------------|-----------|-------------------|---------|
| UL 94 flammability rating | 5VA | Protection degree | IP67 |
| Certificate | CE, cULus | Earth | < 200 g |

Supply voltage

| | |
|--------|---------------------|
| Limits | 18 V DC ... 30 V DC |
|--------|---------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001601 | ETIM 9.0 | EC001601 |
| ETIM 10.0 | EC001601 | ECLASS 14.0 | 27-24-26-05 |
| ECLASS 15.0 | 27-24-26-05 | | |

SAI-AU M12 SB 4PT100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ESG 8/13.5/43.3 SAI AU | Version | |
| Order No. | 1912130000 | ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent, | |
| GTIN (EAN) | 4032248541164 | pluggable | |
| Qty. | 5 ST | | |

M12



Protective caps protect unassigned plug-in stations against external influences.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | SAI-SK-M12-UNI 2029 | Version | |
| Order No. | 2330260000 | Protected component assemblies, Protective cap | |
| GTIN (EAN) | 4032248592067 | | |
| Qty. | 20 ST | | |

M8



Protective caps protect unassigned plug-in stations against external influences.

SAI-AU M12 SB 4PT100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | SAI-SK M8 | Version | |
| Order No. | 1802760000 | Protected component assemblies, Protective cap | |
| GTIN (EAN) | 4032248257379 | | |
| Qty. | 50 ST | | |