



Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### **Product image**















1











Clamping-yoke connection with right-angled (90° or 270°) or angled (225°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. The also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

#### **General ordering data**

| Version      | PCB plug-in connector, female plug, 5.08 mm,<br>Number of poles: 10, 225°, Clamping yoke con-<br>nection, Clamping range, max.: 4 mm², Box |
|--------------|--|
| Order No.    | 1945830000   |
| Туре         | BLZP 5.08HC/10/225B SN OR BX   |
| GTIN (EAN)   | 4032248621309  |
| Qty.         | 30 items   |
| Product data | IEC: 400 V / 17.5 A / 0.2 - 4 mm <sup>2</sup><br>UL: 300 V / 15 A / AWG 26 - AWG 12  |
| Packaging    | Вох  |



Weidmüller Interface GmbH & Co. KG

2

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

## **Approvals**

| Approvals | _ |      |
|-----------|---|------|
|           |   | KEMA |

| ROHS                    | Conform           |
|-------------------------|-------------------|
| UL File Number Search   | <u>UL Website</u> |
| Certificate No. (cURus) | E60693            |

## **Dimensions and weights**

| Depth      | 23.6 mm | Depth (inches)  | 0.9291 inch |
|------------|---------|-----------------|-------------|
| Height     | 15.7 mm | Height (inches) | 0.6181 inch |
| Width      | 52.8 mm | Width (inches)  | 2.0787 inch |
| Net weight | 18.28 g |                 |             |

### **Environmental Product Compliance**

| RoHS Compliance Status | Compliant without exemption |
|------------------------|-----------------------------|
| REACH SVHC             | No SVHC above 0.1 wt%       |

#### **System Parameters**

|  | '                                      |                   |      |        |
|--|--|-------------------|------|--------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08    |                   |      |        |
| Type of connection                           | Field connection                       |                   |      |        |
| Wire connection method                       | Clamping yoke connection               |                   |      |        |
| Pitch in mm (P)                              | 5.08 mm                                |                   |      |        |
| Pitch in inches (P)                          | 0.200 "                                |                   |      |        |
| Conductor outlet direction                   | 225°                                   |                   |      |        |
| Number of poles                              | 10                                     |                   |      |        |
| L1 in mm                                     | 45.72 mm                               |                   |      |        |
| L1 in inches                                 | 1.800 "                                |                   |      |        |
| Number of rows                               | 1                                      |                   |      |        |
| Pin series quantity                          | 1                                      |                   |      |        |
| Rated cross-section                          | 4 mm <sup>2</sup>                      |                   |      |        |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch                 |                   |      |        |
| Touch-safe protection acc. to DIN VDE 0470   | IP20 plugged/ IP10 unplugged           |                   |      |        |
| Protection degree                            | IP20                                   |                   |      |        |
| Volume resistance                            | ≤5 mΩ                                  |                   |      |        |
| Can be coded                                 | Yes                                    |                   |      |        |
| Stripping length                             | 7 mm                                   |                   |      |        |
| Clamping screw                               | M 2.5                                  |                   |      |        |
| Screwdriver blade                            | 0.6 x 3.5, PH 1, PZ 1                  |                   |      |        |
| Screwdriver blade standard                   | DIN 5264, ISO 8764/2-PH, ISO 8764/2-PZ |                   |      |        |
| Plugging cycles                              | 25                                     |                   |      |        |
| Plugging force/pole, max.                    | 10 N                                   |                   |      |        |
| Pulling force/pole, max.                     | 9 N                                    |                   |      |        |
| Tightening torque                            | Torque type                            | Wire connection   |      |        |
|  | Usage information                      | Tightening torque | min. | 0.4 Nm |
|  |  |                   | max. | 0.5 Nm |





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

#### **Material data**

| Insulating material                   | PBT                     | Colour                                | orange    |
|---------------------------------------|-------------------------|---------------------------------------|-----------|
| Colour chart (similar)                | RAL 2000                | Insulating material group             | Illa      |
| Comparative Tracking Index (CTI)      | ≥ 200                   | Moisture Level (MSL)                  |           |
| UL 94 flammability rating             | V-0                     | Contact material                      | Cu-alloy  |
| Contact surface                       | tinned                  | Coating                               | 4-6 μm SN |
| Layer structure of plug contact       | 48 µm Sn hot-dip tinned | Storage temperature, min.             | -40 °C    |
| Storage temperature, max.             | 70 °C                   | Operating temperature, min.           | -50 °C    |
| Operating temperature, max.           | 100 °C                  | Temperature range, installation, min. | -25 °C    |
| Temperature range, installation, max. | 100 °C                  |                                       |           |

| Clamping range, min.                               | 0.13 mm²   |                                  |                          |
|--|--|----------------------------------|--------------------------|
| Clamping range, max.                               | 4 mm <sup>2</sup>  |                                  |                          |
| Wire connection cross section AWG.                 | AWG 30   |                                  |                          |
| nin.   | AVVG 30  |                                  |                          |
| Wire connection cross section AWG,                 | AWG 12   |                                  |                          |
| nax.   | AVVG 12  |                                  |                          |
| Solid, min. H05(07) V-U                            | 0.2 mm <sup>2</sup>  |                                  |                          |
| Solid, max. H05(07) V-U                            | 4 mm²  |                                  |                          |
| Flexible, min. H05(07) V-K                         | 0.2 mm <sup>2</sup>  |                                  |                          |
| Flexible, max. H05(07) V-K                         | 4 mm²  |                                  |                          |
| v. plastic collar ferrule, DIN 46228 pt            |  |                                  |                          |
| nin.   | +, 0.2 mm  |                                  |                          |
| v. plastic collar ferrule, DIN 46228 pt            | 4. 2.5 mm <sup>2</sup>   |                                  |                          |
| nax.   | •  |                                  |                          |
| v. wire end ferrule, DIN 46228 pt 1,               | 0.2 mm <sup>2</sup>  |                                  |                          |
| nin.   |  |                                  |                          |
| v. wire end ferrule, DIN 46228 pt 1,               | 4 mm <sup>2</sup>  |                                  |                          |
| nax.   |  |                                  |                          |
| Plug gauge in accordance with EN<br>60999 a x b; ø | 2.8 mm x 2.4 mm  |                                  |                          |
| Clampable conductor                                | Cross-section for conductor connection   | nominal                          | 0.5 mm <sup>2</sup>      |
|  | wire end ferrule   | Stripping length                 | nominal 6 mm             |
|  |  | Recommended wire-                | H0,5/6                   |
|  |  | end ferrule                      |                          |
|  |  | Stripping length                 | nominal 8 mm             |
|  |  | Recommended wire-<br>end ferrule | H0,5/12 OR               |
|  | Cross-section for conductor connection   | nominal                          | 1 mm <sup>2</sup>        |
|  | wire end ferrule   | Stripping length                 | nominal 6 mm             |
|  |  | Recommended wire-<br>end ferrule | H1,0/6                   |
|  | Cross-section for conductor connection   | nominal                          | 1.5 mm <sup>2</sup>      |
|  | wire end ferrule   | Stripping length                 | nominal 7 mm             |
|  |  | Recommended wire-<br>end ferrule | H1,5/7                   |
|  | Cross-section for conductor connection   | nominal                          | 2.5 mm <sup>2</sup>      |
|  | wire end ferrule   | Stripping length                 | nominal 7 mm             |
|  |  | Recommended wire-                | H2,5/7                   |
|  |  | end ferrule                      |                          |
|  |  | Stripping length                 | nominal 10 mm            |
|  |  | Recommended wire-<br>end ferrule | H2,5/15D BL              |
| Reference text                                     | The outside diameter of the plastic collar should be chosen depending on the product and |                                  | itch (P), Length of ferr |

Creation date 16.11.2025 06:36:29 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| Rated data acc. to IEC  |                        |   |                   |
|---|------------------------|---|-------------------|
|   |                        |   |                   |
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A            |
| Rated current, max. number of poles (Tu=20°C)                             | 14 A                   | Rated current, min. number of poles (Tu=40°C)                         | 14 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 12 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

### Rated data acc. to CSA

| Institute (CSA)                   | CSA    | Certificate No. (CSA)             | 200039-1121690   |
|-----------------------------------|--------|-----------------------------------|--|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group C / CSA) | 50 V   |
| Rated voltage (Use group D / CSA) | 300 V  | Rated current (Use group B / CSA) | 15 A   |
| Rated current (Use group D / CSA) | 15 A   | Wire cross-section, AWG, min.     | AWG 30   |
| Wire cross-section, AWG, max.     | AWG 12 | Reference to approval values      | Specifications are<br>maximum values, details -<br>see approval certificate. |

#### Rated data acc. to UL 1059

| Institute (cURus)                     | CURUS  | Certificate No. (cURus)               | E60693 |
|---------------------------------------|--|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 15 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26   | Wire cross-section, AWG, max.         | AWG 12 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

### **Packing**

| Packaging | Box       | VPE length | 348.00 mm |
|-----------|-----------|------------|-----------|
| VPE width | 135.00 mm | VPE height | 31.00 mm  |

#### Type tests

| Test: Durability of markings                     | Standard       | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96      |
|--|----------------|---|
|  | Test           | mark of origin, rated voltage, rated cross-section, type of material                  |
|  | Evaluation     | available   |
|  | Test           | durability  |
|  | Evaluation     | passed  |
| Test: Misengagement (Non-<br>interchangeability) | Standard       | DIN EN 60512-13-5 / 11.06, IEC 60512-13-5 / 02.06                                     |
|  | Test           | 180° turned with coding elements  |
|  | Evaluation     | passed  |
|  | Test           | visual examination  |
|  | Evaluation     | passed  |
| Test: Clampable cross section                    | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN<br>EN 60947-1 section 8.2.4.5.1 / 12.02 |
|  | Conductor type | Type of conductor solid 0.2 mm <sup>2</sup> and conductor cross-section               |

Creation date 16.11.2025 06:36:29 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Technical data

|                                 |                | Type of conductor stranded 0.2 mm <sup>2</sup> and conductor cross-section          |
|---------------------------------|----------------|---|
|                                 |                | Type of conductor solid 2.5 mm <sup>2</sup> and conductor cross-section             |
|                                 |                | Type of conductor stranded 2.5 mm <sup>2</sup> and conductor cross-section          |
|                                 |                | Type of conductor AWG 26/1 and conductor cross-section                              |
|                                 |                | Type of conductor AWG 26/19 and conductor cross-section                             |
|                                 | Evaluation     | passed  |
| st for damage to and accidental | Standard       | DIN EN 60999-1 section 9.4 / 12.00  |
| osening of conductors           | Requirement    | 0.2 kg  |
|                                 | Conductor type | Type of conductor AWG 26/1 and conductor cross-section  Type of conductor AWG 26/19 |
|                                 |                | and conductor cross-  |
|                                 | F 1 .:         | section   |
|                                 | Evaluation     | passed  |
|                                 | Requirement    | 0.3 kg  |
|                                 | Conductor type | Type of conductor solid 0.5 mm <sup>2</sup> and conductor cross-section             |
|                                 |                | Type of conductor stranded 0.5 mm <sup>2</sup> and conductor cross-section          |
|                                 | Evaluation     | passed  |
|                                 | Requirement    | 0.9 kg  |
|                                 | Conductor type | Type of conductor AWG 12/1 and conductor cross-section                              |
|                                 |                | Type of conductor AWG 12/19 and conductor cross-section                             |
|                                 | Evaluation     | passed  |
| ull-out test                    | Standard       | DIN EN 60999-1 section 9.5 / 12.00  |
|                                 | Requirement    | ≥10 N   |
|                                 | Conductor type | Type of conductor AWG 26/1 and conductor cross-section                              |
|                                 |                | Type of conductor AWG 26/19 and conductor cross-section                             |
|                                 | Evaluation     | passed  |
|                                 | Requirement    | ≥20 N   |
|                                 | Conductor type | Type of conductor H05V-U0.5 and conductor cross-section                             |
|                                 |                | Type of conductor H05V-K0.5 and conductor cross-section                             |
|                                 | Evaluation     | passed  |
|                                 | Requirement    | ≥60 N   |
|                                 | Conductor type | Type of conductor H07V-U4.0 and conductor cross-section                             |





Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

|            | Type of conductor and conductor cross-section | H07V-K4.0 |
|------------|---|-----------|
|            | Type of conductor and conductor cross-section | AWG 12/1  |
|            | Type of conductor and conductor cross-section | AWG 12/19 |
| Evaluation | passed  |           |

#### Important note

IPC conformity


Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- · Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50  $^{\circ}$ C and maximum humidity 70%, 36 months

#### Classifications

| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |
| ECLASS 13.0 | 27-46-02-02 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |





Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

# **Drawings**


### **Product image**



### **Dimensional drawing**



## Graph




#### **Product benefits**



Lower assembly costsSecure in a matter of seconds

#### **Product benefits**



Flexible application optionsFor 3 connection systems



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### Strain reliefs



For frequent load changes: the "trailer coupling" for plugin connectors.

The strain relief can do more than just relieve the strain on conductors:

Simply clip onto the plug and

- bundle conductors
- guide cables
- use as a connection and disconnection aid

No damage to the connecting points, clear, tidy wiring and easy to handle.

User advantages: permanent heavy-duty connections for harsh industrial environments and convenient operation ensure improved system availability.

#### **General ordering data**

| Туре              | BLZ 5.00 ZE04 OR BX               | Version  |
|-------------------|-----------------------------------|--|
| Order No.         | <u>1652100000</u>                 | PCB plug-in connector, Accessories, Strain relief, orange, Number of         |
| GTIN (EAN)        | 4008190401771                     | poles: 4   |
| Qty.              | 50 ST                             |  |
|                   |                                   |  |
| Туре              | BLZ 5.00 ZE08 OR BX               | Version  |
| Type<br>Order No. | BLZ 5.00 ZE08 OR BX<br>1652040000 | Version PCB plug-in connector, Accessories, Strain relief, orange, Number of |
| • •               |                                   |  |

#### **Coding elements**



Only connects what is supposed to be connected: the right connection at the right place.


Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery. Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

#### **General ordering data**

|                   | _                             |   |
|-------------------|-------------------------------|---|
| Туре              | BLZ/SL KO OR BX               | Version   |
| Order No.         | <u>1573010000</u>             | PCB plug-in connector, Accessories, Coding element, orange, Number        |
| GTIN (EAN)        | 4008190048396                 | of poles: 1   |
| Qty.              | 100 ST                        |   |
|                   |                               |   |
| Туре              | BLZ/SL KO BK BX               | Version   |
| Type<br>Order No. | BLZ/SL KO BK BX<br>1545710000 | Version PCB plug-in connector, Accessories, Coding element, black, Number |
|                   | · ·                           |   |

Creation date 16.11.2025 06:36:29 MEZ





Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Slotted screwdriver**



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

#### **General ordering data**

| Type              | SDS 0.6X3.5X100                | Version   |
|-------------------|--------------------------------|---|
| Order No.         | 2749340000                     | Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade         |
| GTIN (EAN)        | 4050118895568                  | thickness (A): 0.6 mm   |
| Qty.              | 1 ST                           |   |
|                   |                                |   |
| Type              | SDIS 0.6X3.5X100               | Version   |
| Type<br>Order No. | SDIS 0.6X3.5X100<br>2749810000 | Version Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
|                   |                                |   |

#### **Crosshead screwdriver Phillips**



Crosshead screwdriver, Phillips, SDK PH DIN 5262, ISO 8764/2-PH, output to ISO 8764-PH, ChromTop tip, SoftFinish grip

### **General ordering data**


| Туре       | SDK PH1 X 80  | Version   |
|------------|---------------|---|
| Order No.  | 2749410000    | Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1 |
| GTIN (EAN) | 4050118895636 |   |
| Qty.       | 1 ST          |   |

### **Crosshead screwdriver Pozidriv**



Crosshead screwdriver, Pozidriv, SDK PZ DIN 5262, ISO 8764/2-PZ, output to ISO 8764/1-PZ, ChromTop tip, SoftFinish grip








Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

## **General ordering data**

| Туре       | SDK PZ1 X 80  | Version   |
|------------|---------------|---|
| Order No.  | 2749440000    | Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1 |
| GTIN (EAN) | 4050118895667 |   |
| Qty.       | 1 ST          |   |





Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SLDF 5.08**



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded.

#### **General ordering data**

 Type
 SLDF 5.08 L/F 10 SN OR ...
 Version

 Order No.
 1599210000
 PCB plug-in connector, male header, 5.08 mm, Number of poles: 10,

 GTIN (EAN)
 4008190065522
 180°, Flat-blade connection, Solder connection, Box

 Qty.
 24 ST

#### SL 5.08/135



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

### **General ordering data**

 Type
 SL 5.08/10/135 3.2SN OR...
 Version

 Order No.
 1603140000
 PCB plug-in connector, male header, open side, THT solder

 GTIN (EAN)
 4008190082123
 connection, 5.08 mm, Number of poles: 10, 135°, Solder pin length

 Qty.
 50 ST
 (I): 3.2 mm, tinned, orange, Box

### SL 5.08/135B



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

#### **General ordering data**

| Туре       | SL 5.08/10/135B 3.2SN O | Version  |
|------------|-------------------------|--|
| Order No.  | <u>1605610000</u>       | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190178284           | solder connection, 5.08 mm, Number of poles: 10, 135°, Solder pin    |
| Qty.       | 50 ST                   | length (I): 3.2 mm, tinned, orange, Box                              |

Creation date 16.11.2025 06:36:29 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### SL 5.08/180



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

### **General ordering data**

 Type
 SL 5.08/10/180 3.2SN OR...
 Version

 Order No.
 1518060000
 PCB plug-in connector, male header, open side, THT solder

 GTIN (EAN)
 4008190122539
 connection, 5.08 mm, Number of poles: 10, 180°, Solder pin length

 Oty.
 50 ST
 (I): 3.2 mm, tinned, orange, Box

#### SL 5.08/180B



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

### **General ordering data**

| Туре       | SL 5.08/10/180B 3.2SN O | Version  |
|------------|-------------------------|--|
| Order No.  | <u>1520360000</u>       | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190030612           | solder connection, 5.08 mm, Number of poles: 10, 180°, Solder pin    |
| Qty.       | 50 ST                   | length (I): 3.2 mm, tinned, orange, Box                              |

### SL 5.08/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

### **General ordering data**

Creation date 16.11.2025 06:36:29 MEZ

| Туре       | SL 5.08/10/90 3.2SN OR | Version   |
|------------|------------------------|---|
| Order No.  | <u>1508860000</u>      | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4008190089092          | connection, 5.08 mm, Number of poles: 10, 90°, Solder pin length (I): |
| Qty.       | 50 ST                  | 3.2 mm, tinned, orange, Box   |



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### SL 5.08/90B



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

#### **General ordering data**

| Туре       | SL 5.08/10/90B 3.2SN OR | Version  |
|------------|-------------------------|--|
| Order No.  | <u>1511160000</u>       | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190052485           | solder connection, 5.08 mm, Number of poles: 10, 90°, Solder pin     |
| Qty.       | 50 ST                   | length (I): 3.2 mm, tinned, orange, Box                              |

#### SL 5.08HC/180



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

#### **General ordering data**

| Type              | SL 5.08HC/10/180 3.2SN               | Version   |
|-------------------|--------------------------------------|---|
| Order No.         | <u>1148290000</u>                    | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN)        | 4032248107773                        | connection, 5.08 mm, Number of poles: 10, 180°, Solder pin length |
| Qty.              | 50 ST                                | (I): 3.2 mm, tinned, black, Box                                   |
|                   |                                      |   |
| Туре              | SL 5.08HC/10/180 3.2SN               | Version   |
| Type<br>Order No. | SL 5.08HC/10/180 3.2SN<br>1146530000 | Version PCB plug-in connector, male header, open side, THT solder |
|                   | , ,                                  |   |

#### SL 5.08HC/180B



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

Creation date 16.11.2025 06:36:29 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **General ordering data**

| Type              | SL 5.08HC/10/180B 3.2SN               | Version  |
|-------------------|---------------------------------------|--|
| Order No.         | 1149670000                            | PCB plug-in connector, male header, Dovetails for fixing blocks, THT         |
| GTIN (EAN)        | 4032248934904                         | solder connection, 5.08 mm, Number of poles: 10, 180°, Solder pin            |
| Qty.              | 50 ST                                 | length (I): 3.2 mm, tinned, black, Box                                       |
|                   |                                       |  |
| Туре              | SL 5.08HC/10/180B 3.2SN               | Version  |
| Type<br>Order No. | SL 5.08HC/10/180B 3.2SN<br>1147580000 | Version PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
|                   |                                       |  |

#### SL 5.08HC/180G



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

#### **General ordering data**

| Туре              | SL 5.08HC/10/180G 3.2SN               | Version   |
|-------------------|---------------------------------------|---|
| Order No.         | <u>1148900000</u>                     | PCB plug-in connector, male header, closed side, THT solder         |
| GTIN (EAN)        | 4032248935369                         | connection, 5.08 mm, Number of poles: 10, 180°, Solder pin length   |
| Qty.              | 50 ST                                 | (I): 3.2 mm, tinned, black, Box                                     |
|                   |                                       |   |
| Type              | SL 5.08HC/10/180G 3.2SN               | Version   |
| Type<br>Order No. | SL 5.08HC/10/180G 3.2SN<br>1146910000 | Version PCB plug-in connector, male header, closed side, THT solder |
|                   | , ,                                   |   |

#### SL 5.08HC/90




Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

#### **General ordering data**

| Туре              | SL 5.08HC/10/90 3.2SN B               | Version   |
|-------------------|---------------------------------------|---|
| Order No.         | 1155130000                            | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN)        | 4050118050738                         | connection, 5.08 mm, Number of poles: 10, 90°, Solder pin length (I): |
| Qty.              | 50 ST                                 | 3.2 mm, tinned, black, Box  |
|                   |                                       |   |
| Type              | SL 5.08HC/10/90 3.2SN O               | Version   |
| Type<br>Order No. | SL 5.08HC/10/90 3.2SN O<br>1146900000 | Version PCB plug-in connector, male header, open side, THT solder     |
|                   | , ,                                   |   |

Creation date 16.11.2025 06:36:29 MEZ





Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SL 5.08HC/90B**



Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

#### **General ordering data**

| Туре       | SL 5.08HC/10/90B 3.2SN               | Version  |
|------------|--------------------------------------|--|
| Order No.  | <u>1155670000</u>                    | PCB plug-in connector, male header, Dovetails for fixing blocks, THT         |
| GTIN (EAN) | 4050118050271                        | solder connection, 5.08 mm, Number of poles: 10, 90°, Solder pin             |
| Qty.       | 50 ST                                | length (I): 3.2 mm, tinned, black, Box                                       |
| -          |                                      |  |
| Type       | SL 5.08HC/10/90B 3.2SN               | Version  |
| Order No.  | SL 5.08HC/10/90B 3.2SN<br>1154850000 | Version PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
|            | , ,                                  |  |

### **SL 5.08HC/90G**



Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

### **General ordering data**

| Туре              | SL 5.08HC/10/90G 3.2SN               | Version   |
|-------------------|--------------------------------------|---|
| Order No.         | <u>1155410000</u>                    | PCB plug-in connector, male header, closed side, THT solder           |
| GTIN (EAN)        | 4050118050509                        | connection, 5.08 mm, Number of poles: 10, 90°, Solder pin length (I): |
| Qty.              | 50 ST                                | 3.2 mm, tinned, black, Box  |
|                   |                                      |   |
| Туре              | SL 5.08HC/10/90G 3.2SN               | Version   |
| Type<br>Order No. | SL 5.08HC/10/90G 3.2SN<br>1147530000 | Version PCB plug-in connector, male header, closed side, THT solder   |
|                   | , ,                                  |   |

Creation date 16.11.2025 06:36:29 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SLDV 5.08/180**



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

#### **General ordering data**

Type SLD 5.08V/20/180 3.2SN ...

Order No. 1725730000 GTIN (EAN)

4032248062027

20 ST

Version

PCB plug-in connector, male header, open side, THT solder connection, 5.08 mm, Number of poles: 20,  $180^{\circ}$ , Solder pin length

(I): 3.2 mm, tinned, orange, Box

#### **SLDV 5.08/180B**

Qty.



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

### **General ordering data**

Туре SLD 5.08V/20/180B 3.2SN... Order No. 1726820000 PCB plug-in connector, male header, Dovetails for fixing blocks, THT GTIN (EAN) 4032248062706 solder connection, 5.08 mm, Number of poles: 20, 180°, Solder pin 20 ST length (I): 3.2 mm, tinned, orange, Box

### **SLDV 5.08/90**



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

#### **General ordering data**

Type SLD 5.08V/20/90 3.2 SN ... Order No. 1725250000 PCB plug-in connector, male header, open side, THT solder GTIN (EAN) 4032248060658 connection, 5.08 mm, Number of poles: 20, 90°, Solder pin length (I): 20 ST 3.2 mm, tinned, orange, Box Qty.

Creation date 16.11.2025 06:36:29 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SLDV 5.08/90B**



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

#### **General ordering data**

| Туре       | SLD 5.08V/20/90B 3.2 SN | Version  |
|------------|-------------------------|--|
| Order No.  | <u>1726360000</u>       | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248061334           | solder connection, 5.08 mm, Number of poles: 20, 90°, Solder pin     |
| Qty.       | 20 ST                   | length (I): 3.2 mm, tinned, orange, Box                              |

#### **SL-SMT 5.08/180 Box**



High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

#### **General ordering data**

| Type              | SL-SMT 5.08HC/10/180 1               | Version   |  |
|-------------------|--------------------------------------|---|--|
| Order No.         | <u>1775682001</u>                    | PCB plug-in connector, male header, open side, THT/THR solder         |  |
| GTIN (EAN)        | 4032248158324                        | connection, 5.08 mm, Number of poles: 10, 180°, Solder pin length     |  |
| Qty.              | 50 ST                                | (I): 1.5 mm, tinned, black, Box                                       |  |
|                   |                                      |   |  |
| Type              | SL-SMT 5.08HC/10/180 3               | Version   |  |
| Type<br>Order No. | SL-SMT 5.08HC/10/180 3<br>1838060000 | Version PCB plug-in connector, male header, open side, THT/THR solder |  |
|                   | , ,                                  |   |  |

#### **SL-SMT 5.08/180G Box**



High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

Creation date 16.11.2025 06:36:29 MEZ





Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

**BLZP 5.08HC/10/225B SN OR BX** 

#### **General ordering data**

| Type              | SL-SMT 5.08HC/10/180G 1               | Version   |
|-------------------|---------------------------------------|---|
| Order No.         | <u>1776002001</u>                     | PCB plug-in connector, male header, closed side, THT/THR solder         |
| GTIN (EAN)        | 4032248158997                         | connection, 5.08 mm, Number of poles: 10, 180°, Solder pin length       |
| Qty.              | 50 ST                                 | (I): 1.5 mm, tinned, black, Box   |
|                   |                                       |   |
| Туре              | SL-SMT 5.08HC/10/180G 3               | Version   |
| Type<br>Order No. | SL-SMT 5.08HC/10/180G 3<br>1838290000 | Version PCB plug-in connector, male header, closed side, THT/THR solder |
|                   | , , ,                                 |   |

#### **SL-SMT 5.08HC/90 Box**



High-temperature-resistant, 90° angled, open male header. Packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

#### **General ordering data**

| Туре              | SL-SMT 5.08HC/10/90 1.5               | Version   |
|-------------------|---------------------------------------|---|
| Order No.         | <u>1774842001</u>                     | PCB plug-in connector, male header, open side, THT/THR solder         |
| GTIN (EAN)        | 4032248155880                         | connection, 5.08 mm, Number of poles: 10, 90°, Solder pin length (I): |
| Qty.              | 50 ST                                 | 1.5 mm, tinned, black, Box  |
|                   |                                       |   |
| Type              | SL-SMT 5.08HC/10/90 3.2               | Version   |
| Type<br>Order No. | SL-SMT 5.08HC/10/90 3.2<br>1780030000 | Version PCB plug-in connector, male header, open side, THT/THR solder |
|                   | , ,                                   |   |

#### **SL-SMT 5.08HC/90G Box**



High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

#### **General ordering data**

| Туре              | SL-SMT 5.08HC/10/90G 1               | Version   |
|-------------------|--------------------------------------|---|
| Order No.         | <u>1775082001</u>                    | PCB plug-in connector, male header, closed side, THT/THR solder         |
| GTIN (EAN)        | 4032248156559                        | connection, 5.08 mm, Number of poles: 10, 90°, Solder pin length (I):   |
| Qty.              | 50 ST                                | 1.5 mm, tinned, black, Box  |
|                   |                                      |   |
| Туре              | SL-SMT 5.08HC/10/90G 1               | Version   |
| Type<br>Order No. | SL-SMT 5.08HC/10/90G 1<br>1775083001 | Version PCB plug-in connector, male header, closed side, THT/THR solder |
|                   |                                      |   |

Creation date 16.11.2025 06:36:29 MEZ





Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

| Туре       | SL-SMT 5.08HC/10/90G 3 | Version   |
|------------|------------------------|---|
| Order No.  | <u>1780260000</u>      | PCB plug-in connector, male header, closed side, THT/THR solder       |
| GTIN (EAN) | 4032248165582          | connection, 5.08 mm, Number of poles: 10, 90°, Solder pin length (I): |
| Qty.       | 50 ST                  | 3.2 mm, tinned, black, Box  |

#### **SLF 5.08/180 SN**



Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through The male plugs provide space for labelling and can be coded.

#### **General ordering data**

| Туре              | SLF 5.08/10/180 SN BK BX               | Version   |
|-------------------|--|---|
| Order No.         | 1335710000                             | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,         |
| GTIN (EAN)        | 4050118139143                          | 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm², Box       |
| Qty.              | 36 ST                                  |   |
|                   |  |   |
| Туре              | SLF 5.08/10/180 SN OR BX               | Version   |
| Type<br>Order No. | SLF 5.08/10/180 SN OR BX<br>1335410000 | Version PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10, |
|                   |  |   |

## **SLF 5.08/180B SN**



Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through The male plugs provide space for labelling and can be coded.

### **General ordering data**

| SLF 5.08/10/180B SN BK | Version  |
|------------------------|--|
| <u>1335940000</u>      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,              |
| 4050118138993          | 180°, PUSH IN with actuator, Clamping range, max.: 3.31 mm², Box             |
| 30 ST                  |  |
| SLF 5.08/10/180B SN OR | Version  |
| <u>1335530000</u>      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,              |
| 4050118139044          | 180°, PUSH IN with actuator, Clamping range, max.: 3.31 mm², Box             |
| 00.07                  |  |
|                        | 1335940000<br>4050118138993<br>30 ST<br>SLF 5.08/10/180B SN OR<br>1335530000 |

Creation date 16.11.2025 06:36:29 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SLF 5.08/180DF SN**



Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through The male plugs provide space for labelling and can be coded.

#### General ordering data

24 ST

Qty.

 Type
 SLF 5.08/10/180DF SN OR...
 Version

 Order No.
 1353680000
 PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,

 GTIN (EAN)
 4050118156423
 180°, PUSH IN with actuator, Clamping range, max.: 3.31 mm², Box

#### **SLT 5.08/180DF SN**



Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.

### **General ordering data**

 Type
 SLT 5.08/10/180DF SN OR...
 Version

 Order No.
 1353450000
 PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,

 GTIN (EAN)
 4050118156102
 180°, TOP connection, Clamping range, max.: 2.5 mm², Box

 Qty.
 24 ST

### **SLT 5.08B**



Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.

#### **General ordering data**

Creation date 16.11.2025 06:36:29 MEZ

 Type
 SLT 5.08/10/180B SN OR ...
 Version

 Order No.
 1611790000
 PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,

 GTIN (EAN)
 4008190192679
 180°, TOP connection, Clamping range, max. : 2.5 mm², Box

 Oty.
 50 ST



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SLS 5.08/180 SN**



Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

#### **General ordering data**

| Туре       | SLS 5.08/10/180 SN OR BX | Version  |
|------------|--------------------------|--|
| Order No.  | 1627170000               | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,  |
| GTIN (EAN) | 4008190199685            | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², |
| Qty.       | 36 ST                    | Вох  |

#### **SLS 5.08/180B**




Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

#### **General ordering data**

| Туре       | SLS 5.08/10/180B SN OR | Version   |
|------------|------------------------|---|
| Order No.  | <u>1627320000</u>      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4008190199838          | 180°, Clamping yoke connection, Clamping range, max.: 3.31 mm², |
| Qty.       | 30 ST                  | Вох   |

## **SLS 5.08/180DF SN**



Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

### **General ordering data**

Creation date 16.11.2025 06:36:29 MEZ

| Туре       | SLS 5.08/10/180DF SN OR | Version   |
|------------|-------------------------|---|
| Order No.  | <u>1353570000</u>       | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4050118156294           | 180°, Clamping yoke connection, Clamping range, max.: 3.31 mm², |
| Qty.       | 24 ST                   | Вох   |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Counterpart

#### **SLS 5.08TB KF35**



Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

#### **General ordering data**

| Туре       | SLS 5.08/10/180TB KF SN | Version  |
|------------|-------------------------|--|
| Order No.  | <u>1846160000</u>       | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10,  |
| GTIN (EAN) | 4032248362448           | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², |
| Qty.       | 10 ST                   | Вох  |

#### **SLS 5.08TB RF15**



Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

## **General ordering data**

| Туре       | SLS 5.08/10/180TB RF15 | Version   |
|------------|------------------------|---|
| Order No.  | 1846080000             | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4032248362363          | 180°, Clamping yoke connection, Clamping range, max.: 3.31 mm², |
| Qty.       | 10 ST                  | Вох   |