

HSS-HF 3/8 5.8-8.0/25Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor markers, Conductor and cable markers, 5.8 - 8 mm, 25.4 x 16 mm, yellow
Order No.	1962000000
Type	HSS-HF 3/8 5.8-8.0/25Y
GTIN (EAN)	4032248642694
Qty.	4000 items

HSS-HF 3/8 5.8-8.0/25Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	25.4 mm	Height (inches)	1 inch
Width	16 mm	Width (inches)	0.6299 inch
Net weight	0.59 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	Type of printing	neutral
Width	16 mm	Operating temperature range, max.	105 °C
Operating temperature range, min.	-55 °C	Colour	yellow
Halogen	No	Basic material	Polyolefine
Printed characters compatible printer	without THM MULTIMARK , THM MULTIMARK PLUS	Recommended industries	Transportation
		Operating temperature range	-55...105 °C

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	10 mm ²	Conductor O.D., max.	8 mm
Conductor O.D., min.	5.8 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Text field width	25.4 mm
Text field height	15.25 mm	Conductor O.D.	5.8 - 8 mm
Cross-section for connected wire	10 - 16 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HSS-HF 3/8 5.8-8.0/25Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



Bestellhilfe

HSS-HF 1/8" 1,2-2,8 / 50 Y

- Y = Gelb (W=Weiß)
- 50,8 mm Hüslenlänge (oder 25,4 mm)
- geeigneter Leiterdurchmesser 1,2 - 2,8mm
- Max. Außendurchmesser 1/8" (bzw. 3,2 mm)
- HF = Halogenfrei nach VDE 0472-615
- HSS = Heat Shrinkable Sleeve (wärmeschrumpfender Schlauch)