Data sheet

SAIL-M12BG-B-USB-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNetTM, EtherCAT and Ethernet.

General ordering data

Version	Bus line, Connecting line, M12, Number of poles: 5, 1.5 m, Male, straight - female, straight, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No
Order No.	1962800150
Type	SAIL-M12BG-B-USB-1.5U
GTIN (EAN)	4032248644896
Qty.	1 items

Data sheet

SAIL-M12BG-B-USB-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Length	1.5 mm	Length (inches)	0.0591 inch
Net weight	68 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

Technical specifications for cable

Cable length	1.5 m	Sheathing colour	black
Resistance to oils	No	Suitable for cable carriers	Yes
Core cross-section	0.09 mm²	Number of wires	4
Shielded	Yes	Halogen	No
Insulation	PE	Bending radius, min., stationary	5 x cable diameter
Resistance to spread of flame	UL Style 20963	Sheath material	PUR
Cable length configurable	No	Outer cladding in accordance with UL AWM style	20963 (80 °C / 30 V)
Type is hybrid cable	No	Irradiation crosslinked	No
Colour coding	white, green, red, black	Number of poles	5

General technical data

Connection thread	M12	Contact surface	Gold-plated
LED	No	Version	Male, straight - female, straight
Housing main material	PUR	Insulation resistance	≥ 20 MΩ
Nominal voltage	5 V	Nominal current	1 A
Protection degree	IP20	Pollution severity	3
Threaded ring material	Nickel-plated CuZn	Temperature range of housing	-25...+80 °C
Tightening torque	M12: 0.8 - 1.2 Nm		

Electrical properties

Insulation resistance	≥ 20 MΩ	Nominal voltage	5 V

Cable structure

Sheathing colour	black	Cross-section	2*AWG28 + 2*AWG28
Shielding	360° all-round enclosure	Number of wires	4
Insulation	PE	Colour coding	white, green, red, black

Electrical properties of cable

Insulation resistance	≥ 20 MΩ	Category	Miscellaneous
Nominal current	1 A		

SAIL-M12BG-B-USB-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Mechanical and material properties of cable

Resistance to oils	No	Halogen	No
Resistance to spread of flame	UL Style 20963		

Plug, left

Plug left	M12, B-coded, Number of poles: 5, female contact, straight, plug, shielded

Plug, right

Plug right	USB A, Number of poles: 4, IP20, male contact, straight, plug, shielded

Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-07		


SAIL-M12BG-B-USB-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Drawings

Dimensioned drawing




Straight socket

Pole scheme



M12, socket, B-coded

Dimensioned drawing



USB type A


SAIL-M12BG-B-USB-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram



The ideal tool: Screwty ® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F