


**HSS-HF 3/4 11.0-17.0/50Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor markers, Conductor and cable markers, 11 - 17 mm, 50.8 x 31.8 mm, yellow
Order No.	<a href="#">1961950000</a>
Type	HSS-HF 3/4 11.0-17.0/50Y
GTIN (EAN)	4032248642649
Qty.	1250 items

## HSS-HF 3/4 11.0-17.0/50Y

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	50.8 mm	Height (inches)	2 inch
Width	31.8 mm	Width (inches)	1.252 inch
Net weight	2.68 g		

### Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Material colour according to resistance code	4	Type of printing	neutral
Width	31.8 mm	Operating temperature range, max.	105 °C
Operating temperature range, min.	-55 °C	Colour	yellow
Halogen	No	Basic material	Polyolefine
Printed characters compatible printer	without <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	Recommended industries	Transportation
		Operating temperature range	-55...105 °C

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	35 mm <sup>2</sup>	Conductor O.D., max.	17 mm
Conductor O.D., min.	11 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Text field width	50.8 mm
Text field height	30.54 mm	Conductor O.D.	11 - 17 mm
Cross-section for connected wire	35 - 70 mm <sup>2</sup>		

### Classifications


ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**HSS-HF 3/4 11.0-17.0/50Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



Bestellhilfe

**HSS-HF 1/8" 1,2-2,8 / 50 Y**

- Y = Gelb (W=Weiß)
- 50,8 mm Hüslenlänge (oder 25,4 mm)
- geeigneter Leiterdurchmesser 1,2 - 2,8mm
- Max. Außendurchmesser 1/8" (bzw. 3,2 mm)
- HF = Halogenfrei nach VDE 0472-615
- HSS = Heat Shrinkable Sleeve (wärmeschrumpfender Schlauch)