



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

#### **Product image**






















OMNIMATE Power BU / SU 10.16HP - the 50 kVA power class

More current for higher performance.

Top of the class in today's connector systems – the OMNIMATE Power SU / BUZ 10.16HP. They feature a very durable contact system which makes it a pluggable power transmission solution with maximum load reserves. HP stands for High Performance – performance exemplified by a long-term usage temperature of 120°C. This custom, pluggable solution is suitable for all applications that must meet 600 V UL or 1,000 V (IEC) with up to 76 A (IEC) and 54 A (UL).

#### **General ordering data**

Packaging	UL: 600 V / 57 A / AWG 24 - AWG 6		
Product data	IEC: 1000 V / 78 A / 0.2 - 16 mm <sup>2</sup>		
Qty.	16 items		
GTIN (EAN)	4032248644438		
Туре	SUZ 10.16HP/08/180G AG BK BX		
Order No.	<u>1962400000</u>		
Version	PCB plug-in connector, male plug, 10.16 mm, Number of poles: 8, 180°, Clamping yoke connec- tion, Clamping range, max. : 16 mm², Box		





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

#### **Approvals**

Approvals



ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (UR)	E60693

#### **Dimensions and weights**

Net weight 94.48 g

#### **Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

#### **System Parameters**

Product family	OMNIMATE Power - series BU/SU 10.16HP	Type of connection	Field connection
Wire connection method	Clamping yoke connection	Pitch in mm (P)	10.16 mm
Pitch in inches (P)	0.400 "	Conductor outlet direction	180°
Number of poles	8	L1 in mm	71.12 mm
L1 in inches	2.800 "	Number of rows	1
Pin series quantity	1	Rated cross-section	16 mm²
Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch	Touch-safe protection acc. to DIN VDE 0470	IP 20
Volume resistance	4.50 mΩ	Can be coded	Yes
Stripping length	12 mm	Tightening torque, min.	1.2 Nm
Tightening torque, max.	1.5 Nm	Clamping screw	M 4
Screwdriver blade	1.0 x 5.5	Screwdriver blade standard	DIN 5264
Plugging cycles	25		

#### **Material data**

Insulating material	PA GF	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	
Comparative Tracking Index (CTI)	≥ 600	Moisture Level (MSL)	
UL 94 flammability rating	V-0	Contact material	Cu-alloy
Contact surface	silver-plated	Layer structure of plug contact	≥ 3 µm Ag
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	130 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	130 °C

#### **Conductors suitable for connection**

Clamping range, min.	0.2 mm <sup>2</sup>
Clamping range, max.	16 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 22
Wire connection cross section AWG, max.	AWG 6
Solid, min. H05(07) V-U	0.2 mm <sup>2</sup>
Solid, max. H05(07) V-U	16 mm <sup>2</sup>

Creation date 30.11.2025 07:27:58 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Technical data

rechnical data			
Stranded, min. H07V-R	6 mm <sup>2</sup>		
Stranded, max. H07V-R	16 mm <sup>2</sup>		
Flexible, min. H05(07) V-K	0.5 mm <sup>2</sup>		
Flexible, max. H05(07) V-K	16 mm <sup>2</sup>		
w. plastic collar ferrule, DIN 46228 pt 4	1, 0.25 mm²		
min.			
w. plastic collar ferrule, DIN 46228 pt 4 max.			
w. wire end ferrule, DIN 46228 pt 1, min.	0.25 mm <sup>2</sup>		
w. wire end ferrule, DIN 46228 pt 1, max.	16 mm <sup>2</sup>		
Plug gauge in accordance with EN 60999 a x b; ø	5.3mm (B6)		
Clampable conductor	Cross-section for conductor connection	Туре	fine-wired
		nominal 0.5 mm <sup>2</sup>	
	wire end ferrule	Stripping length	nominal 14 mm
		Recommended wire- end ferrule	H0,5/18 OR
	Cross-section for conductor connection	Туре	fine-wired
		nominal	1 mm <sup>2</sup>
	wire end ferrule	Stripping length	nominal 15 mm
		Recommended wire- end ferrule	H1,0/18 GE
	Cross-section for conductor connection	Туре	fine-wired
	Order decision for demander definitions.	nominal	1.5 mm <sup>2</sup>
	wire end ferrule	Stripping length	nominal 15 mm
		Recommended wire-	H1,5/18D SW
			nominal 12 mm
		Stripping length Recommended wire-	H1,5/12
	Construction for a substantian	end ferrule	£
	Cross-section for conductor connection	Type	fine-wired
	in- and famile	nominal	0.75 mm <sup>2</sup>
	wire end ferrule	Stripping length	nominal 14 mm
		Recommended wire- end ferrule	H0,75/18 W
	Cross-section for conductor connection	Туре	fine-wired
		nominal	2.5 mm <sup>2</sup>
	wire end ferrule	Stripping length	nominal 14 mm
		Recommended wire- end ferrule	H2,5/19D BL
		Stripping length	nominal 12 mm
		Recommended wire- end ferrule	H2,5/12
	Cross-section for conductor connection	Туре	fine-wired
		nominal	4 mm <sup>2</sup>
	wire end ferrule	Stripping length	nominal 12 mm
		Recommended wire- end ferrule	H4,0/12
		Stripping length	nominal 14 mm
		Recommended wire-	H4,0/20D GR
	Cross-section for conductor connection		fina wirod
	Gross-section for conductor connection	Type	fine-wired 6 mm <sup>2</sup>
	wire end ferrule	nominal Stripping length	
	wile ella lellale	Stripping length  Recommended wire-	nominal
		end ferrule	nominal 12
		Stripping length	nominal 12 mm





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

	Recommended wire- end ferrule	H6,0/12	
Cross-section for conductor connection	Type	fine-wired	
	nominal	10 mm <sup>2</sup>	
wire end ferrule	Stripping length	nominal	12 mm
	Recommended wire- end ferrule	H10,0/12	
	Stripping length	nominal	15 mm
	Recommended wire- end ferrule	H10,0/22	<u>EB</u>
Cross-section for conductor connection	Type	fine-wired	
	nominal	16 mm <sup>2</sup>	
wire end ferrule	Stripping length	nominal	12 mm
	Recommended wire- end ferrule	H16,0/12	

Reference text Length of ferrules is to be chosen depending on the product and the rated voltage.

#### Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	78 A
Rated current, max. number of poles (Tu=20°C)	68 A	Rated current, min. number of poles (Tu=40°C)	72 A
Rated current, max. number of poles (Tu=40°C)	61 A	Rated voltage for surge voltage class / pollution degree II/2	1000 V
Rated voltage for surge voltage class / pollution degree III/2	1000 V	Rated voltage for surge voltage class / pollution degree III/3	1000 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	6 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	8 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	8 kV	Short-time withstand current resistance	3 x 1s with 800A
Creepage distance, min.	14.8 mm	Clearance, min.	14.8 mm

#### Rated data acc. to CSA

Institute (CSA)	CSA	Certificate No. (CSA)	200039-1121690
Rated voltage (Use group B / CSA)	600 V	Rated voltage (Use group C / CSA)	600 V
Rated voltage (Use group D / CSA)	600 V	Rated current (Use group B / CSA)	57 A
Rated current (Use group C / CSA)	57 A	Rated current (Use group D / CSA)	5 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 6
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

#### Rated data acc. to UL 1059

Institute (UR)	UR	Certificate No. (UR)	E60693
Rated voltage (Use group B / UL 1059)	600 V	Rated voltage (Use group C / UL 1059)	600 V
Rated voltage (Use group D / UL 1059)	600 V	Rated current (Use group B / UL 1059)	57 A
Rated current (Use group C / UL 1059)	57 A	Rated current (Use group D / UL 1059)	5 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 6
Reference to approval values	Specifications are maximum values, details -		

#### **Packing**

Packaging	Box	VPE length	352.00 mm
VPE width	135.00 mm	VPE height	60.00 mm

Creation date 30.11.2025 07:27:58 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### Technical data

Type tests		
Test: Durability of markings	Standard	taking pattern from DIN EN 60068-2-70 / 07.9
	Test	date clock, mark of origin, type identification, type of material
	Evaluation	available
	Test	durability
	Evaluation	passed
Test: Misengagement (Non- interchangeability)	Standard	DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN IEC 60512 part 7 section 5 / 05.94
	Test	180° turned with coding elements
	Evaluation	passed
	Test	180° turned without coding elements
	Evaluation	passed
est: Clampable cross section	Standard	DIN EN 60999-1 section 7 and 9.1 / 12.00, D EN 60947-1 section 8.2.4.5.1 / 12.02
	Conductor type	Type of conductor solid 0.2 mm <sup>2</sup> and conductor cross-
		section
		Type of conductor stranded 0.2 mm <sup>2</sup> and conductor cross-
		section
		Type of conductor solid 16 mm <sup>2</sup>
		and conductor cross-
		section
		Type of conductor stranded 16 mm <sup>2</sup>
		and conductor cross- section
		Type of conductor AWG 24/1
		and conductor cross-
		section
		Type of conductor AWG 24/19 and conductor cross-
		section
		Type of conductor AWG 6/1 and conductor cross-section
		Type of conductor AWG 6/19
		and conductor cross- section
	Evaluation	passed
est for damage to and accidental	Standard	DIN EN 60999-1 section 9.4 / 12.00
posening of conductors	Requirement	0.2 kg
	Conductor type	Type of conductor AWG 24/1 and conductor cross-
		section Type of conductor AWG 24/19
		and conductor cross-
		section
	Evaluation	passed
	Requirement	0.3 kg
	Conductor type	Type of conductor solid 0.5 mm <sup>2</sup> and conductor cross-
		Section  Type of conductor stranded 0.5 mm <sup>2</sup>
		and conductor cross- section
	Evaluation	passed
	Requirement	2.9 kg
	Conductor type	Type of conductor solid 16 mm <sup>2</sup>

Catalogue status / Drawings 5

and conductor cross-

section



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

		Type of conductor stranded 16 mm <sup>2</sup> and conductor cross-section
	Evaluation	passed
	Requirement	0,9 kg
	Conductor type	Type of conductor AWG 6/7 and conductor cross-section
		Type of conductor AWG 6/19 and conductor cross-section
	Evaluation	passed
ull-out test	Standard	DIN EN 60999-1 section 9.5 / 12.00
	Requirement	≥10 N
	Conductor type	Type of conductor AWG 24/1 and conductor cross-section
		Type of conductor AWG 24/19 and conductor cross-section
	Evaluation	passed
	Requirement	≥20 N
	Conductor type	Type of conductor solid 0.5 mm <sup>2</sup> and conductor cross-section
		Type of conductor stranded 0.5 mm <sup>2</sup> and conductor cross-section
	Evaluation	passed
	Requirement	≥100 N
	Conductor type	Type of conductor solid 16 mm <sup>2</sup> and conductor cross-section
		Type of conductor stranded 16 mm <sup>2</sup> and conductor cross-section
		Type of conductor AWG 6/7 and conductor cross-section
		Type of conductor AWG 6/19 and conductor cross-section
	Evaluation	passed


#### Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products
	can be evaluated on request.
Mates	Additional variants on remund

- Notes Additional variants on request
  - Rated current related to rated cross-section & min. No. of poles.
  - Wire end ferrule without plastic collar to DIN 46228/1
  - Wire end ferrule with plastic collar to DIN 46228/4
  - P on drawing = pitch
  - Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
  - In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
  - Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Creation date 30.11.2025 07:27:58 MEZ







Weidmüller Interface GmbH & Co. KG

7

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

#### Classifications

ETIM 6.0	EC002638	ETIM 7.0	EC002638
ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 9.0	27-44-03-09
ECLASS 9.1	27-44-03-09	ECLASS 10.0	27-44-03-09
ECLASS 11.0	27-46-02-02	ECLASS 12.0	27-46-02-02
ECLASS 13.0	27-46-02-02	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

# **Drawings**

#### **Product image**



## Dimensional drawing



#### Graph

