

IE-PS-V04P-RJ45-FH-BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with RJ45 insert

General ordering data

Version	RJ45 plug, no tools required, Version 4, anti-kink device, Cat.6A / Class EA (ISO/IEC 11801 2010)
Order No.	1963170000
Type	IE-PS-V04P-RJ45-FH-BP
GTIN (EAN)	4032248653980
Qty.	10 items

IE-PS-V04P-RJ45-FH-BP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

Dimensions and weights

Net weight 39.1 g

Temperatures

Storage temperature Operating temperature -40 °C...70 °C

Installation temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

General data

Connection 1	RJ45	Connection 2	IDC
Description of article	Version 4, anti-kink device	Colour	black
Housing main material	PA UL 94 V0	Insulation cross-section, min.	0.85 mm
Insulation cross-section, max.	1.6 mm	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact surface	Gold over nickel	Connection diameter, solid	0.4...0.64 mm
Conductor connection cross-section, solid (AWG)	AWG 24...AWG 22	Connection diameter, flexible	0.48...0.76 mm
Conductor connection cross-section, flexible (AWG)	AWG 26...AWG 22	MICE classification M	M3
MICE classification I	I3	MICE classification C	C1
MICE classification E	E3	Sheath diameter, min.	5 mm
Sheath diameter, max.	10 mm	Shielding	360°; all-round enclosure
Protection degree	IP67	Plugging cycles	750
Ability to reconnect	≥ 10 cycles (for the same or larger cross-section)		

Electrical properties

Dielectric strength, contact / shield ≥ 1500 V AC/DC Dielectric strength, contact / contact ≥ 1000 V AC/DC

General standards

Connector standard	IEC 61076-3-106 Var. 4, IEC 60603-7-5 1	Application-specific communication cable facilities	PROFINET installation instructions
Certificate no. (cULus)	E316369		

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90

Creation date 19.03.2026 02:25:27 MEZ

Catalogue status / Drawings

Technical data

ECLASS 15.0

27-44-03-90


IE-PS-V04P-RJ45-FH-BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing



IE-PS-V04P-RJ45-FH-BP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Dust caps




For protecting your devices against dust and dirt.

General ordering data

Type	IE-PP-V04P	Version	
Order No.	1963890000	Plug housing protective cap	
GTIN (EAN)	4032248646319		
Qty.	10 ST		

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 9/11 K MC NE WS	Version	
Order No.	1857440000	ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive	
GTIN (EAN)	4032248402731		
Qty.	200 ST		

