

IE-PM-RJ45-TH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



RJ45 crimp plug-in connector according to IEC
60603-7-51 for wire outer diameters up to 1.05 mm

General ordering data

Version	RJ45 crimp plug, Plug without bending protection sleeve, Cat.6A / Class EA (ISO/IEC 11801 2010)
Order No.	1963580000
Type	IE-PM-RJ45-TH
GTIN (EAN)	4032248645688
Qty.	100 items

IE-PM-RJ45-TH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E316369

Dimensions and weights

Net weight	3.46 g
------------	--------

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Connection 1	RJ45	Connection 2	Crimp
Description of article	Plug without bending protection sleeve	Composition	Connects piercing contacts and shielded connections in one step, retro-fit for kink-prevention sleeves, Multi-port compatible
Colour	Miscellaneous	Insulation cross-section, min.	0.85 mm
Insulation cross-section, max.	1.05 mm	Cable pull-out force, min.	89 N
Category	Cat.6A / Class EA (ISO/IEC 11801 2010)	Contact material	Phosphorus bronze
Contact surface	Gold-plated	Connection diameter, solid	0.36...0.51 mm
Conductor connection cross-section, solid (AWG)	AWG 27...AWG 24	Connection diameter, flexible	0.46...0.61 mm
Conductor connection cross-section, flexible (AWG)	AWG 27...AWG 24	MICE classification M	M1
MICE classification I	I1	MICE classification C	C1
MICE classification E	E3	Sheath diameter, min.	5 mm
Sheath diameter, max.	7.3 mm	Bending protection sleeve material	Polycarbonate PC, UL 94 V-0
Shielding material	0.5 mm brass, 2 µm nickel	Shielding	360°; all-round enclosure
Protection degree	IP20	Plugging cycles	750
Material insulator	Polycarbonate PC, UL 94 V-0		

Electrical properties

Contact resistance	≤ 20 mΩ	Dielectric strength, contact / shield	≥ 1500 V AC/DC
Dielectric strength, contact / contact	≥ 1000 V AC/DC	Insulation resistance	500 MΩ
Current-carrying capacity at 50 °C	1 A	PoE / PoE+	conforming to IEEE 802.3af

Technical data**General standards**

Certificate No. (cURus)	E316369	Connector standard	IEC 60603-7-51
-------------------------	---------	--------------------	----------------

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Drawings

Dimensioned drawing

