

IE-KO-HAT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

Not suitable for stainless steel!

General ordering data

Version	Sheet holes
Order No.	1966810000
Type	IE-KO-HAT
GTIN (EAN)	4032248659630
Qty.	1 items

IE-KO-HAT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	120 mm	Height (inches)	4.7244 inch
Width	290 mm	Width (inches)	11.4173 inch
Net weight	3262 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	Hydraulic sheet holes
------------------------	-----------------------

Cutting tools

Max. operating pressure	680 bar	Type hydraulic oil	HLP32
Round holes from 1 to Ø 85 mm	2,0 mm F = 370 N/mm ²	Round holes from 2 to Ø 64 mm	3,0 mm F = 370 N/mm ²
Punching force	75 kN	Round holes from 3 to Ø 64 mm	2.5 mm F = 600 N/mm ²
Rectangular holes up to	36 x 112 mm; 2,0 mm F = 370 N/mm ²	Square holes up to	68 x 68 mm; 2.0 mm F = 370 N/mm ²

Classifications

ETIM 8.0	EC000156	ETIM 9.0	EC000156
ETIM 10.0	EC000156	ECLASS 14.0	21-04-51-16
ECLASS 15.0	21-04-51-16		

IE-KO-HAT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

