

**SAIL-M12BG-CD-0.3A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, Ether-CAT and Ethernet.

**General ordering data**

|            |  |
|------------|--|
| Version    | Bus line, One end without connector, M12, Number of poles: 5, 0.3 m, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">1964690030</a>   |
| Type       | SAIL-M12BG-CD-0.3A   |
| GTIN (EAN) | 4050118560572  |
| Qty.       | 1 items  |

## SAIL-M12BG-CD-0.3A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Net weight 29.92 g

### Environmental Product Compliance

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 1c533b66-fcff-4da5-b89f-fd55fbf5cb55

### Technical specifications for cable

|  |   |                               |                     |
|--|---|-------------------------------|---------------------|
| Cable length                                   | 0.3 m   | Sheathing colour              | violet              |
| Suitable for cable carriers                    | Yes   | Shielded                      | Yes                 |
| Halogen  | No  | Insulation                    | TPE                 |
| Acceleration                                   | 5 m/s <sup>2</sup>                                  | Bending radius, min., moving  | 10 x cable diameter |
| Bending radius, min., stationary               | 5 x cable diameter                                  | Bending cycles                | 3 Mio               |
| Wire cross section (Print/Online)              | 2 x 0.34 mm <sup>2</sup> + 2 x 0.22 mm <sup>2</sup> | Speed                         | 180 m/s             |
| Sheath material                                | PUR   | Configurable cable length     | No                  |
| Outer cladding in accordance with UL AWM style | 20236 (80 °C / 30 V)                                | Hybrid cable                  | No                  |
| Irradiation crosslinked                        | No  | Welding spark resistance      | No                  |
| Colour coding                                  | white, blue, red, black                             | Temperature range, stationary | -40...80 °C         |
| Resistant to welding beads                     | No  | Temperature range, moving     | -10...80 °C         |
| Number of poles                                | 5   | Outside diameter              | 7 mm ± 0.3 mm       |

### General technical data

|                        |                      |                              |              |
|------------------------|----------------------|------------------------------|--------------|
| Coding                 | A-coded              | Connection thread            | M12          |
| Contact surface        | Gold-plated          | LED                          | No           |
| Housing main material  | PUR                  | Insulation resistance        | 108 Ω        |
| Nominal voltage        | 125 V                | Nominal current              | 4 A          |
| Protection degree      | IP67                 | Plugging cycles              | ≥ 100        |
| Pollution severity     | 3                    | jumpered                     | No           |
| Threaded ring material | Brass, nickel-plated | Temperature range of housing | -25...+80 °C |
| Tightening torque      | M12: 0.8 - 1.2 Nm    |                              |              |

### Electrical properties

Insulation resistance 108 Ω      Nominal voltage 125 V

### Plug, left

Plug left M12, A-coded, IP67, female contact, straight, Plastic, shielded

**SAIL-M12BG-CD-0.3A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Plug, right**

|            |                    |
|------------|--------------------|
| Plug right | free conductor end |
|------------|--------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 |             |             |

Drawings

Pole scheme



Socket



Socket

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

