



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image

























Power on board - 100% safety, 100% integration, 100% cost-effectiveness:

The compact, efficient solution for UL-600V applications in the lower performance range.

High-performance female header for applications up to 12 kVA:

- 29 A with 400 V (IEC)
- 20 A at 600 V (UL)
- 0.08 4 mm² / AWG 28 12


Assisting in device approval:

- Meets the requirements of 600 V according to UL 508 / UL 840.
- When plugged, meets the increased requirements on touch safety as per IEC 68100-5-1

The slimming diet for multiple-stage device series: Reduce the size and cut costs in the high-volume lower performance range without compromising device approval!

General ordering data

Version	PCB plug-in connector, female plug, 7.62 mm,	
	Number of poles: 2, 180°, Clamping yoke connection, Clamping range, max.: 4 mm², Box	
Order No.	<u>1980480000</u>	
Туре	BLZ 7.62HP/02/180 SN OR BX	
GTIN (EAN)	4032248675531	
Qty.	100 items	
Product data	IEC: 630 V / 29 A / 0.2 - 4 mm ²	
	UL: 600 V / 20 A / AWG 20 - AWG 12	
Packaging	Вох	





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	F60693

Dimensions and weights

Depth	23.3 mm	Depth (inches)	0.9173 inch
Height	18.3 mm	Height (inches)	0.7205 inch
Width	14.52 mm	Width (inches)	0.5717 inch
Net weight	4.28 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.090 kg CO2eq.

System Parameters

Product family	OMNIMATE Power - series BL/SL 7.62HP	Type of connection	Field connection
Wire connection method	Clamping yoke connection	Pitch in mm (P)	7.62 mm
Pitch in inches (P)	0.300 "	Conductor outlet direction	180°
Number of poles	2	L1 in mm	7.62 mm
L1 in inches	0.300 "	Number of rows	1
Pin series quantity	1	Rated cross-section	2.5 mm ²
Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch	Touch-safe protection acc. to DIN VDE 0470	IP 20
Protection degree	IP20	Volume resistance	5.00 mΩ
Can be coded	Yes	Stripping length	7 mm
Tightening torque, min.	0.4 Nm	Tightening torque, max.	0.5 Nm
Clamping screw	M 2.5	Screwdriver blade	0.6 x 3.5
Screwdriver blade standard	DIN 5264	Plugging cycles	25
Plugging force/pole, max.	9.5 N	Pulling force/pole, max.	8.5 N

Material data

Insulating material	PBT	Colour	orange
Colour chart (similar)	RAL 2000	Insulating material group	Illa
Comparative Tracking Index (CTI)	≥ 200	Insulation resistance	≥ 108 Ω
Moisture Level (MSL)		UL 94 flammability rating	V-0
Contact material	Cu-alloy	Contact surface	tinned
Layer structure of plug contact	48 µm Sn hot-dip tinned	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	100 °C		

Conductors suitable for connection

Clamping range, min.	0.08 mm ²
Clamping range, max.	4 mm ²

Creation date 30.11.2025 11:29:59 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Wire connection cross section AWG,	AWG 28	
min.		
Wire connection cross section AWG, max.	AWG 12	
Solid, min. H05(07) V-U	0.2 mm ²	
Solid, max. H05(07) V-U	4 mm²	
Flexible, min. H05(07) V-K	0.2 mm ²	
Flexible, max. H05(07) V-K	4 mm ²	
w. plastic collar ferrule, DIN 46228 pt		
min.		
w. plastic collar ferrule, DIN 46228 pt max.	4, 2.5 mm²	
w. wire end ferrule, DIN 46228 pt 1, min.	0.2 mm ²	
w. wire end ferrule, DIN 46228 pt 1, max.	2.5 mm ²	
Plug gauge in accordance with EN 60999 a x b; ø	2.8 mm x 2.4 mm	
Clampable conductor	Cross-section for conductor connection	Type fine-wired
		nominal 0.25 mm ²
	wire end ferrule	Stripping length nominal 10 mm
		Recommended wire- H0,25/12 HBL end ferrule
	Cross-section for conductor connection	Type fine-wired
		nominal 0.34 mm ²
	wire end ferrule	Stripping length nominal 10 mm
		Recommended wire- H0,34/12 TK
		end ferrule
	Cross-section for conductor connection	Type fine-wired
		nominal 0.5 mm ²
	wire end ferrule	Stripping length nominal 6 mm
		Recommended wire- H0.5/6 end ferrule
	Cross-section for conductor connection	Type fine-wired
	Greek seemen for semanation seminosium.	nominal 0.75 mm ²
	wire end ferrule	Stripping length nominal 6 mm
	This one is a	Recommended wire- end ferrule
	Cross-section for conductor connection	Type fine-wired
	Greek seemen for semanation seminosium.	nominal 1 mm ²
	wire end ferrule	Stripping length nominal 6 mm
	Wile sha ishale	Recommended wire- end ferrule
	Cross-section for conductor connection	Type fine-wired
	Closs-section for conductor connection	nominal 1.5 mm ²
	wire end ferrule	
	wile ellu lellule	Stripping length nominal 7 mm Recommended wire- H1,5/7
		end ferrule
	Cross-section for conductor connection	Type fine-wired
		nominal 2.5 mm ²
	wire end ferrule	Stripping length nominal 7 mm
		Recommended wire- H2,5/7 end ferrule
Reference text	The outside diameter of the plastic collar shows is to be chosen depending on the product and	uld not be larger than the pitch (P), Length of ferrules d the rated voltage.

Creation date 30.11.2025 11:29:59 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Rated	data	acc.	to	IEC
-------	------	------	----	-----

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	29 A
Rated current, max. number of poles Tu=20°C)	26.5 A	Rated current, min. number of poles (Tu=40°C)	25 A
Rated current, max. number of poles (Tu=40°C)	23 A	Rated voltage for surge voltage class / pollution degree II/2	630 V
Rated voltage for surge voltage class / pollution degree III/2	500 V	Rated voltage for surge voltage class / pollution degree III/3	400 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	6 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	6 kV	Short-time withstand current resistance	3 x 1s with 180 A
Creepage distance, min.	11.3 mm	Clearance, min.	9.8 mm

Rated data acc. to CSA

Institute (CSA)	CSA	Certificate No. (CSA)	200039-1121690
Rated voltage (Use group B / CSA)	600 V	Rated voltage (Use group C / CSA)	600 V
Rated voltage (Use group D / CSA)	600 V	Rated current (Use group B / CSA)	20 A
Rated current (Use group C / CSA)	20 A	Rated current (Use group D / CSA)	5 A
Wire cross-section, AWG, min.	AWG 20	Wire cross-section, AWG, max.	AWG 12
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Rated data acc. to UL 1059

Institute (cURus)	CURUS	Certificate No. (cURus)	E60693
Rated voltage (Use group B / UL 1059)	600 V	Rated voltage (Use group C / UL 1059)	600 V
Rated voltage (Use group D / UL 1059)	600 V	Rated current (Use group B / UL 1059)	20 A
Rated current (Use group C / UL 1059)	20 A	Rated current (Use group D / UL 1059)	5 A
Wire cross-section, AWG, min.	AWG 20	Wire cross-section, AWG, max.	AWG 12
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Packing

Packaging	Box	VPE length	138.00 mm
VPE width	95.00 mm	VPE height	77.00 mm

Type tests

Test: Durability of markings	Standard	DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96	
	Test	mark of origin, type identification, pitch, type of material, date clock	
	Evaluation	available	
	Test	durability	
	Evaluation	passed	
Test: Misengagement (Non- interchangeability)	Standard	DIN EN 61984 section 6.3 and 6.9.1 / 09.02	
	Test	180° turned with coding elements	
	Evaluation	passed	
	Test	180° turned without coding elements	
	Evaluation	passed	
Test: Clampable cross section	Standard	DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02	

Creation date 30.11.2025 11:29:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

	Conductor type	Type of conductor solid 0.5 mm ² and conductor cross-section
		Type of conductor stranded 0.5 mm ² and conductor cross-section
		Type of conductor solid 2.5 mm ² and conductor cross-section
		Type of conductor stranded 2.5 mm ² and conductor cross-section
		Type of conductor AWG 20/1 and conductor cross-section
		Type of conductor AWG 20/19 and conductor cross-section
		Type of conductor AWG 12/1 and conductor cross-section
		Type of conductor AWG 12/19 and conductor cross-section
	Evaluation	passed
est for damage to and accidental	Standard	DIN EN 60999-1 section 9.4 / 12.00
loosening of conductors	Requirement Conductor type	0.2 kg Type of conductor AWG 28/1 and conductor cross- section
		Type of conductor AWG 28/19 and conductor cross-section
	Evaluation	passed
	Requirement	0.3 kg
	Conductor type	Type of conductor H05V-U0.5 and conductor cross- section
		Type of conductor H05V-K0.5 and conductor cross- section
	Evaluation	passed
	Requirement	0.7 kg
	Conductor type	Type of conductor AWG 14/1 and conductor cross-section
		Type of conductor AWG 14/19 and conductor cross-section
	Evaluation	passed
	Requirement	0.9 kg
	Conductor type	Type of conductor H07V-U4.0 and conductor cross-section
		Type of conductor H07V-K4.0 and conductor cross-section
	Evaluation	passed
ull-out test	Standard	DIN EN 60999-1 section 9.5 / 12.00
	Requirement Conductor type	≥5 N Type of conductor AWG 28/1 and conductor cross- section



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

	Type of conductor and conductor cross-section	AWG 28/19	
Evaluation	passed		
Requirement	≥20 N		
Conductor type	Type of conductor and conductor cross-section	H05V-U0.5	
	Type of conductor and conductor cross-section	H05V-K0.5	
Evaluation	passed		
Requirement	≥50 N		
Conductor type	Type of conductor and conductor cross-section	AWG 14/1	
	Type of conductor and conductor cross-section	AWG 14/19	
	Type of conductor and conductor cross-section	H07V-K4.0	
Evaluation	passed		
Requirement	≥60 N		
Conductor type	Type of conductor and conductor cross-section	H07V-U4.0	
Evaluation	passed		

Important note

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

ETIM 6.0	EC002638	ETIM 7.0	EC002638
ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 9.0	27-44-03-09
ECLASS 9.1	27-44-03-09	ECLASS 10.0	27-44-03-09
ECLASS 11.0	27-46-02-02	ECLASS 12.0	27-46-02-02
ECLASS 13.0	27-46-02-02	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com


Drawings

Product image




Dimensional drawing

Graph



Graph



BLZ 7.62HP/../180 - SL 7.62HP/../90 S 1 20 25 20 15 10 5 2 2 pon. 15 2 2 pon. 16 2 12 pon. 2 2 pon. 3 2 pon. 3 2 pon. 4 2 pon. 3 2 pon. 4 2 pon. 5 2 pon. 5 2 pon. 6 2 pon. 7 2 pon.