


## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Product image



Just as reliable as the millionfold proven original and featuring innovative details:

The BLF 5.08HC PUSH IN version of the BLZP 5.08HC female connector is not only different in terms of connection system; it also has a more compact design. Weidmüller's innovative PUSH IN spring connection system stands for the future of easy and tool-free wire connection. HC = High Current.

In terms of versatility, the BLF 5.08HC offers just as much as the version which served as a model:

- 3 tested-and-proven wire outlet directions provide the usual flexibility for application-specific design
- 4 flange variations and the patented release latch allow the locking concept to be based on the requirements of the user
- Use the BLF 5.08HC and SL 5.08HC plug combination to reach the max. rated specifications

## General ordering data

|              |  |
|--------------|--|
| Version      | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 16, 270°, PUSH IN with actuator, Clamping range, max. : 3.31 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1982840000</a>   |
| Type         | BLF 5.08HC/16/270 SN OR BX   |
| GTIN (EAN)   | 4032248686933  |
| Qty.         | 18 items   |
| Product data | IEC: 400 V / 24 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 18.5 A / AWG 26 - AWG 12  |
| Packaging    | Box  |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E60693                     |

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 26.2 mm  | Depth (inches)  | 1.0315 inch |
| Height     | 20.6 mm  | Height (inches) | 0.811 inch  |
| Width      | 81.28 mm | Width (inches)  | 3.2 inch    |
| Net weight | 31.55 g  |                 |             |

## Environmental Product Compliance

|                          |   |
|--------------------------|---|
| RoHS Compliance Status   | Compliant without exemption                 |
| REACH SVHC               | No SVHC above 0.1 wt%                       |
| Product Carbon Footprint | Cradle to gate 1,006 kg CO <sub>2</sub> eq. |

## System Parameters

|  |                                     |  |                              |
|--|-------------------------------------|--|------------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08 | Type of connection                         | Field connection             |
| Wire connection method                       | PUSH IN with actuator               | Pitch in mm (P)                            | 5.08 mm                      |
| Pitch in inches (P)                          | 0.200 "                             | Conductor outlet direction                 | 270°                         |
| Number of poles                              | 16                                  | L1 in mm                                   | 76.20 mm                     |
| L1 in inches                                 | 3.000 "                             | Number of rows                             | 1                            |
| Pin series quantity                          | 1                                   | Rated cross-section                        | 2.5 mm <sup>2</sup>          |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Protection degree                            | IP20                                | Volume resistance                          | ≤5 mΩ                        |
| Can be coded                                 | Yes                                 | Stripping length                           | 10 mm                        |
| Screwdriver blade                            | 0.6 x 3.5                           | Screwdriver blade standard                 | DIN 5264                     |
| Plugging cycles                              | 25                                  | Plugging force/pole, max.                  | 7 N                          |
| Pulling force/pole, max.                     | 5.5 N                               |  |                              |

## Material data

|                                       |          |                                       |                            |
|---------------------------------------|----------|---------------------------------------|----------------------------|
| Insulating material                   | PBT      | Colour                                | orange                     |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | IIIa                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Moisture Level (MSL)                  |                            |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-alloy                   |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -30 °C   | Temperature range, installation, max. | 100 °C                     |

## Conductors suitable for connection

|   |                      |
|---|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 3.31 mm <sup>2</sup> |
| Wire connection cross section AWG, min. | AWG 26               |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Wire connection cross section AWG, AWG 12 max.

Solid, min. H05(07) V-U 0.2 mm<sup>2</sup>

Solid, max. H05(07) V-U 2.5 mm<sup>2</sup>

Flexible, min. H05(07) V-K 0.2 mm<sup>2</sup>

Flexible, max. H05(07) V-K 2.5 mm<sup>2</sup>

w. plastic collar ferrule, DIN 46228 pt 4, 0.25 mm<sup>2</sup> min.

w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm<sup>2</sup> max.

w. wire end ferrule, DIN 46228 pt 1, 0.25 mm<sup>2</sup> min.

w. wire end ferrule, DIN 46228 pt 1, 2.5 mm<sup>2</sup> max.

Plug gauge in accordance with EN 60999 a x b; ø 2.8 mm x 2.0 mm

## Clampable conductor

## Cross-section for conductor connection

Type fine-wired

nominal 0.5 mm<sup>2</sup>

## wire end ferrule

Stripping length nominal 12 mm

Recommended wire-end ferrule [H0,5/16 OR](#)

Stripping length nominal 10 mm

Recommended wire-end ferrule [H0,5/10](#)

## Cross-section for conductor connection

Type fine-wired

nominal 0.75 mm<sup>2</sup>

## wire end ferrule

Stripping length nominal 12 mm

Recommended wire-end ferrule [H0,75/16 W](#)

Stripping length nominal 10 mm

Recommended wire-end ferrule [H0,75/10](#)

## Cross-section for conductor connection

Type fine-wired

nominal 1 mm<sup>2</sup>

## wire end ferrule

Stripping length nominal 12 mm

Recommended wire-end ferrule [H1,0/16D R](#)

Stripping length nominal 10 mm

Recommended wire-end ferrule [H1,0/10](#)

## Cross-section for conductor connection

Type fine-wired

nominal 1.5 mm<sup>2</sup>

## wire end ferrule

Stripping length nominal 10 mm

Recommended wire-end ferrule [H1,5/10](#)

Stripping length nominal 12 mm

Recommended wire-end ferrule [H1,5/16 R](#)

## Cross-section for conductor connection

nominal 2.5 mm<sup>2</sup>

## wire end ferrule

Stripping length nominal 10 mm

Recommended wire-end ferrule [H2,5/10](#)

Stripping length nominal 13 mm

Recommended wire-end ferrule [H2,5/16DS BL](#)

## Reference text

The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Rated data acc. to IEC

|   |                        |   |                   |
|---|------------------------|---|-------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 24 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 19 A                   | Rated current, min. number of poles (Tu=40°C)                         | 21 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 16.5 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## Rated data acc. to CSA

|                                   |  |                                   |                |
|-----------------------------------|--|-----------------------------------|----------------|
| Institute (CSA)                   | CSA  | Certificate No. (CSA)             | 200039-1121690 |
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 10 A   | Rated current (Use group D / CSA) | 10 A           |
| Wire cross-section, AWG, min.     | AWG 12   | Wire cross-section, AWG, max.     | AWG 26         |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |                                   |                |

## Rated data acc. to UL 1059

|                                       |  |                                       |        |
|---------------------------------------|--|---------------------------------------|--------|
| Institute (cURus)                     | CURUS  | Certificate No. (cURus)               | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 18.5 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26   | Wire cross-section, AWG, max.         | AWG 12 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

## Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 351.00 mm |
| VPE width | 142.00 mm | VPE height | 31.00 mm  |

## Type tests

|  |                |  |
|--|----------------|--|
| Test: Durability of markings                 | Standard       | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96   |
|  | Test           | mark of origin, type identification, pitch, type of material, date clock           |
|  | Evaluation     | available  |
|  | Test           | durability   |
|  | Evaluation     | passed   |
| Test: Misengagement (Non-interchangeability) | Standard       | DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN EN 60512-13-5 / 11.08              |
|  | Test           | 180° turned with coding elements   |
|  | Evaluation     | passed   |
|  | Test           | visual examination   |
|  | Evaluation     | passed   |
| Test: Clampable cross section                | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 04.08 |
|  | Conductor type | Type of conductor solid 0.2 mm <sup>2</sup> and conductor cross-section            |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

|   |   |   |
|---|---|---|
| Test for damage to and accidental loosening of conductors | Type of conductor and conductor cross-section | stranded 0.2 mm <sup>2</sup>                            |
|   | Type of conductor and conductor cross-section | solid 2.5 mm <sup>2</sup>                               |
|   | Type of conductor and conductor cross-section | stranded 2.5 mm <sup>2</sup>                            |
|   | Type of conductor and conductor cross-section | AWG 26/1  |
|   | Type of conductor and conductor cross-section | AWG 26/19   |
|   | Type of conductor and conductor cross-section | AWG 14/1  |
|   | Type of conductor and conductor cross-section | AWG 14/19   |
|   | Evaluation                                    | passed  |
|   | Standard                                      | DIN EN 60999-1 section 9.4 / 12.00                      |
|   | Requirement                                   | 0.2 kg  |
| Pull-out test   | Conductor type                                | Type of conductor AWG 26/1 and conductor cross-section  |
|   | Conductor type                                | Type of conductor AWG 26/19 and conductor cross-section |
|   | Evaluation                                    | passed  |
|   | Requirement                                   | 0.3 kg  |
|   | Conductor type                                | Type of conductor H05V-U0.5 and conductor cross-section |
|   | Conductor type                                | Type of conductor H05V-K0.5 and conductor cross-section |
|   | Evaluation                                    | passed  |
|   | Requirement                                   | 0.7 kg  |
|   | Conductor type                                | Type of conductor H07V-U2.5 and conductor cross-section |
|   | Conductor type                                | Type of conductor H07V-K2.5 and conductor cross-section |
|   | Evaluation                                    | passed  |
|   | Requirement                                   | 0.9 kg  |
|   | Conductor type                                | Type of conductor AWG 12/1 and conductor cross-section  |
|   | Conductor type                                | Type of conductor AWG 12/19 and conductor cross-section |
|   | Evaluation                                    | passed  |
|   | Standard                                      | DIN EN 60999-1 section 9.5 / 12.00                      |
|   | Requirement                                   | ≥10 N   |
|   | Conductor type                                | Type of conductor AWG 26/1 and conductor cross-section  |
|   | Conductor type                                | Type of conductor AWG 26/19 and conductor cross-section |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

|                |   |           |
|----------------|---|-----------|
| Evaluation     | passed  |           |
| Requirement    | $\geq 20$ N                                   |           |
| Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|                | Type of conductor and conductor cross-section | H05V-K0.5 |
| Evaluation     | passed  |           |
| Requirement    | $\geq 50$ N                                   |           |
| Conductor type | Type of conductor and conductor cross-section | H07V-U2.5 |
|                | Type of conductor and conductor cross-section | H07V-K2.5 |
| Evaluation     | passed  |           |
| Requirement    | $\geq 60$ N                                   |           |
| Conductor type | Type of conductor and conductor cross-section | AWG 12/1  |
|                | Type of conductor and conductor cross-section | AWG 12/19 |
| Evaluation     | passed  |           |

## Important note

## IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

## Notes

- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.
- The test point can only be used as potential-pickup point.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months



## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |


**BLF 5.08HC/16/270 SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Product image****Dimensional drawing**

MIN. FRONT PLATE CUT-OUT


**Graph**

Uncompromising functionalityHigh vibration resistance

**BLF 5.08HC/16/270 SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Product benefits**

Solid PUSH IN contactSafe and durable

**Product benefits**

Cost-effective wiring Quick and intuitive operation

**Product benefits**

Wide clamping range Tool-free wire connection

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Coding elements



Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery.

Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | BLZ/SL KO BK BX            | Version  |
| Order No.  | <a href="#">1545710000</a> | PCB plug-in connector, Accessories, Coding element, black, Number  |
| GTIN (EAN) | 4008190087142              | of poles: 1  |
| Qty.       | 50 ST                      |  |
| Type       | BLZ/SL KO OR BX            | Version  |
| Order No.  | <a href="#">1573010000</a> | PCB plug-in connector, Accessories, Coding element, orange, Number |
| GTIN (EAN) | 4008190048396              | of poles: 1  |
| Qty.       | 100 ST                     |  |

## Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SDS 0.6X3.5X100            | Version   |
| Order No.  | <a href="#">2749340000</a> | Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118895568              | thickness (A): 0.6 mm   |
| Qty.       | 1 ST                       |   |
| Type       | SDS 0.6X3.5X200            | Version   |
| Order No.  | <a href="#">9010110000</a> | Screwdriver, Screwdriver  |
| GTIN (EAN) | 4032248300754              |   |
| Qty.       | 1 ST                       |   |
| Type       | SDIS 0.6X3.5X100           | Version   |
| Order No.  | <a href="#">2749810000</a> | Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118897012              | thickness (A): 0.6 mm   |
| Qty.       | 1 ST                       |   |


## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SLDF 5.08



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLDF 5.08 L/F 16 SN OR ... | Version   |
| Order No.  | <a href="#">1599270000</a> | PCB plug-in connector, male header, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4008190066826              | 180°, Flat-blade connection, Solder connection, Box               |
| Qty.       | 18 ST                      |   |

## SL 5.08/135



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL 5.08/16/135 3.2SN OR... | Version   |
| Order No.  | <a href="#">1603200000</a> | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN) | 4008190123635              | connection, 5.08 mm, Number of poles: 16, 135°, Solder pin length |
| Qty.       | 50 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |

## SL 5.08/135B



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SL 5.08/16/135B 3.2SN O... | Version  |
| Order No.  | <a href="#">1605670000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190153816              | solder connection, 5.08 mm, Number of poles: 16, 135°, Solder pin    |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |


## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SL 5.08/180



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL 5.08/16/180 3.2SN OR... | Version   |
| Order No.  | <a href="#">1518660000</a> | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN) | 4008190083304              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |

## SL 5.08/180B



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SL 5.08/16/180B 3.2SN O... | Version  |
| Order No.  | <a href="#">1520960000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190145149              | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin    |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |

## SL 5.08/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL 5.08/16/90 3.2SN OR ... | Version   |
| Order No.  | <a href="#">1509460000</a> | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4008190147464              | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty.       | 50 ST                      | 3.2 mm, tinned, orange, Box   |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SL 5.08/90B




Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SL 5.08/16/90B 3.2SN OR... | Version  |
| Order No.  | <a href="#">1511760000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190020552              | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin     |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |

## SL 5.08HC/180




Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL 5.08HC/16/180 3.2SN ... | Version   |
| Order No.  | <a href="#">1148410000</a> | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN) | 4032248934867              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (l): 3.2 mm, tinned, black, Box                                   |
| Type       | SL 5.08HC/16/180 3.2SN ... | Version   |
| Order No.  | <a href="#">1146610000</a> | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN) | 4032248933518              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |

## SL 5.08HC/180B



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SL 5.08HC/16/180B 3.2SN... | Version  |
| Order No.  | <a href="#">1149870000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248934263              | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin    |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, black, Box                               |
| Type       | SL 5.08HC/16/180B 3.2SN... | Version  |
| Order No.  | <a href="#">1147770000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248933747              | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin    |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |

## SL 5.08HC/180G




Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL 5.08HC/16/180G 3.2SN... | Version   |
| Order No.  | <a href="#">1149100000</a> | PCB plug-in connector, male header, closed side, THT solder       |
| GTIN (EAN) | 4032248935017              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (l): 3.2 mm, tinned, black, Box                                   |
| Type       | SL 5.08HC/16/180G 3.2SN... | Version   |
| Order No.  | <a href="#">1147040000</a> | PCB plug-in connector, male header, closed side, THT solder       |
| GTIN (EAN) | 4032248934065              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |

## SL 5.08HC/90



Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL 5.08HC/16/90 3.2SN B... | Version   |
| Order No.  | <a href="#">1155200000</a> | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4050118050677              | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty.       | 50 ST                      | 3.2 mm, tinned, black, Box  |
| Type       | SL 5.08HC/16/90 3.2SN O... | Version   |
| Order No.  | <a href="#">1147030000</a> | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4050118051360              | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty.       | 50 ST                      | 3.2 mm, tinned, orange, Box   |


## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SL 5.08HC/90B




Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SL 5.08HC/16/90B 3.2SN ... | Version  |
| Order No.  | <a href="#">1155730000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4050118050219              | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin     |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, black, Box                               |
| Type       | SL 5.08HC/16/90B 3.2SN ... | Version  |
| Order No.  | <a href="#">1154920000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4050118050905              | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin     |
| Qty.       | 50 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |

## SLDV 5.08/180




Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLD 5.08V/32/180 3.2SN ... | Version   |
| Order No.  | <a href="#">1725790000</a> | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN) | 4032248062089              | connection, 5.08 mm, Number of poles: 32, 180°, Solder pin length |
| Qty.       | 10 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |

## SLDV 5.08/180B



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SLD 5.08V/32/180B 3.2SN... | Version  |
| Order No.  | <a href="#">1726880000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248062775              | solder connection, 5.08 mm, Number of poles: 32, 180°, Solder pin    |
| Qty.       | 10 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |

## SLDV 5.08/90



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLD 5.08V/32/90 3.2 SN ... | Version   |
| Order No.  | <a href="#">1725310000</a> | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4032248060719              | connection, 5.08 mm, Number of poles: 32, 90°, Solder pin length (l): |
| Qty.       | 10 ST                      | 3.2 mm, tinned, orange, Box   |

## SLDV 5.08/90B



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SLD 5.08V/32/90B 3.2 SN... | Version  |
| Order No.  | <a href="#">1726420000</a> | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248061396              | solder connection, 5.08 mm, Number of poles: 32, 90°, Solder pin     |
| Qty.       | 10 ST                      | length (l): 3.2 mm, tinned, orange, Box                              |


## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SL-SMT 5.08/180 Box




High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL-SMT 5.08HC/16/180 3...  | Version   |
| Order No.  | <a href="#">1838120000</a> | PCB plug-in connector, male header, open side, THT/THR solder     |
| GTIN (EAN) | 4032248348183              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (I): 3.2 mm, tinned, black, Box                                   |

## SL-SMT 5.08/180G Box



High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL-SMT 5.08HC/16/180G 3... | Version   |
| Order No.  | <a href="#">1838350000</a> | PCB plug-in connector, male header, closed side, THT/THR solder   |
| GTIN (EAN) | 4032248348411              | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty.       | 50 ST                      | (I): 3.2 mm, tinned, black, Box                                   |

## SL-SMT 5.08HC/90 Box



High-temperature-resistant, 90° angled, open male header. Packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL-SMT 5.08HC/16/90 1.5... | Version   |
| Order No.  | <a href="#">1774902001</a> | PCB plug-in connector, male header, open side, THT/THR solder         |
| GTIN (EAN) | 4032248155842              | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (I): |
| Qty.       | 50 ST                      | 1.5 mm, tinned, black, Box  |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL-SMT 5.08HC/16/90 3.2... | Version   |
| Order No.  | <a href="#">1780090000</a> | PCB plug-in connector, male header, open side, THT/THR solder         |
| GTIN (EAN) | 4032248165414              | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty.       | 50 ST                      | 3.2 mm, tinned, black, Box  |

## SL-SMT 5.08HC/90G Box




High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SL-SMT 5.08HC/16/90G 3.... | Version   |
| Order No.  | <a href="#">1780320000</a> | PCB plug-in connector, male header, closed side, THT/THR solder       |
| GTIN (EAN) | 4032248165643              | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty.       | 50 ST                      | 3.2 mm, tinned, black, Box  |

## SLT 5.08B



Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SLT 5.08/16/180B SN OR ... | Version  |
| Order No.  | <a href="#">1611850000</a> | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16,        |
| GTIN (EAN) | 4008190192730              | 180°, TOP connection, Clamping range, max. : 2.5 mm <sup>2</sup> , Box |
| Qty.       | 50 ST                      |  |


## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SLS 5.08/180 SN




Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLS 5.08/16/180 SN OR BX   | Version   |
| Order No.  | <a href="#">1627230000</a> | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16,               |
| GTIN (EAN) | 4008190199746              | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm <sup>2</sup> , |
| Qty.       | 18 ST                      | Box   |

## SLS 5.08/180B



Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLS 5.08/16/180B SN OR ... | Version   |
| Order No.  | <a href="#">1627380000</a> | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16,               |
| GTIN (EAN) | 4008190199890              | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm <sup>2</sup> , |
| Qty.       | 18 ST                      | Box   |

## SLS 5.08TB KF35



Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLS 5.08/16/180TB KF SN... | Version   |
| Order No.  | <a href="#">1846180000</a> | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16,               |
| GTIN (EAN) | 4032248362462              | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm <sup>2</sup> , |
| Qty.       | 5 ST                       | Box   |

## BLF 5.08HC/16/270 SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Counterpart

## SLS 5.08TB RF15



Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SLS 5.08/16/180TB RF15 ... | Version   |
| Order No.  | <a href="#">1846100000</a> | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16,               |
| GTIN (EAN) | 4032248362387              | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm <sup>2</sup> , |
| Qty.       | 5 ST                       | Box   |