

## HDC CM BUS SV M2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The ConCept-CSB module is a double module and takes up two slots in the ConCept module frame. The ConCept-CSB module consists of a module carrier that is capable of holding two contact carriers. The contact carrier is manufactured with a die-cast zinc alloy which provides it with excellent shielding capabilities. The crimp contacts are insulated from the contact carrier and mounted in a plastic insert. A variety of pole counts – 1, 4 and 8 poles – are available to ensure compatibility with a wide range of applications.

### General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1983750000</a>
Type	HDC CM BUS SV M2
GTIN (EAN)	4032248688913
Qty.	1 items

## HDC CM BUS SV M2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

### Dimensions and weights

Height	28.5 mm	Height (inches)	1.122 inch
Width	22.8 mm	Width (inches)	0.8976 inch
Length	34 mm	Length (inches)	1.3386 inch
Net weight	7.92 g		

### Temperatures

Limit temperature -40 °C ... 70 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

### ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	beige
---------------------------	-----	--------	-------

### Dimensions

Width	22.8 mm	Total length base	34 mm
Height of plug	28.5 mm		

### General data

Number of poles	2	Type of connection	Crimp connection
UL 94 flammability rating	V-0	Colour	beige
Plugging cycles	≥ 500	Type	Pin
Basic material	Polycarbonate	Series	ConCept module
Rated voltage (DIN EN 61984)	50 V	Rated current (DIN EN 61984)	10 A
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes

### Version

Type of connection	Crimp connection	Basic material	Polycarbonate
--------------------	------------------	----------------	---------------

### Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-18
ECLASS 15.0	27-44-02-18		

**HDC CM BUS SV M2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

