


HDC CFM 24 7F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The sturdy CR24 module frames are available in polycarbonate or die-cast zinc.

The frames are designed so that 7 individual modules or corresponding double modules can be installed. dementsprechende The CR24 frames are designed to fit the size-8 housings.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	1983900000
Type	HDC CFM 24 7F
GTIN (EAN)	4032248689033
Qty.	1 items

HDC CFM 24 7F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

Dimensions and weights

Depth	110 mm	Depth (inches)	4.3307 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.3386 inch
Net weight	100 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
SCIP	fa505316-3e43-4ad0-930c-360dfdbe182a

ConCept Pneumatic module

Colour Silver grey

Dimensions

Width	34 mm	Total length base	111 mm
Height of socket	35 mm		

General data

Installation size	8	Colour	Silver grey
Type	Female	Basic material	Diecast zinc
Series	ConCept frame	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes	BG	8

Connection data PE

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	0.5 Nm		

Version

Installation size	8	Basic material	Diecast zinc
BG	8		

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02

Creation date 18.02.2026 12:35:38 MEZ

Catalogue status / Drawings

Technical data

ECLASS 15.0

27-44-02-02
