

RCL314024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Similar to illustration

Individual relays for TERMSERIES

- Electromechanical relays
- Different contact materials

General ordering data

Version	TERMSERIES, Relay, Number of contacts: 1, CO contact AgNi, Rated control voltage: 24 V DC, Continuous current: 16 A, Plug-in connection, Test button available: No
Order No.	1984040000
Type	RCL314024W
GTIN (EAN)	4050118369366
Qty.	20 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E302101

Dimensions and weights

Depth	15.7 mm	Depth (inches)	0.6181 inch
Height	29 mm	Height (inches)	1.1417 inch
Width	12.7 mm	Width (inches)	0.5 inch
Net weight	14 g		

Temperatures

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...70 °C
Operating temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Certificate No. (cURus)	E302101
-------------------------	---------

Control side

Rated control voltage	24 V DC	Rated current DC	17.3 mA
Power rating	420 mW	Coil resistance	1440 Ω ± 10 %
Status indicator	No		

Load side

Rated switching voltage	250 V AC	Continuous current	16 A
Max. switching frequency at rated load	0.1 Hz	Inrush current	30 A / 4 s
AC switching capacity (resistive), max.	4000 VA	DC switching capacity (resistive), max.	384 W @ 24 V
Switch-on delay	≤ 8 ms	Switch-off delay	≤ 4 ms
Contact type	1 CO contact (AgNi)	Min. switching power	1 mA @ 24 V, 10 mA @ 12 V, 100 mA @ 5 V

General data

Test button available	No	Mechanical switch position indicator	No
Colour	white		

Insulation coordination

Rated voltage	400 V	Pollution severity	3
Surge voltage category	III	Clearance and creepage distances for control side - load side	≥ 10 mm

RCL314024W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dielectric strength for control side - load 1.2 kVeff / 5 s
side

Dielectric strength of open contact 1 kVeff / 1 min

Protection degree IP20

Further details of approvals / standards

Certificate No. (cURus) E302101

Connection data


Wire connection method Plug-in connection Pitch in mm (P) 5.00 mm

Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		


Drawings

Wiring diagram




View of Pins from below

Graph




DC load limit curve Resistive load

Graph




Electrical service life

Dimensional drawing



Miscellaneous



Type codes

RCL314024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart

Screw connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOS 24VDC EMPTY	Version
Order No.	1127720000	TERMSERIES, Relay socket, Rated control voltage: 24 V DC $\pm 20\%$,
GTIN (EAN)	4032248909377	Rated switching voltage: 230 V AC, Continuous current: 16 A, Screw
Qty.	10 ST	connection

Tension clamp connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOZ 24VDC EMPTY	Version
Order No.	1127740000	TERMSERIES, Relay socket, Rated control voltage: 24 V DC $\pm 20\%$,
GTIN (EAN)	4032248909421	Rated switching voltage: 230 V AC, Continuous current: 16 A,
Qty.	10 ST	Tension-clamp connection

Screw connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOS 24-230VUC EMPTY	Version
Order No.	1127730000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC $\pm 10\%$,
GTIN (EAN)	4032248909254	Rated switching voltage: 230 V AC, Continuous current: 16 A,
Qty.	10 ST	Screw connection

RCL314024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart

Tension clamp connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOZ 24-230VUC EMPTY	Version	
Order No.	1127750000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC ±10	
GTIN (EAN)	4032248909223	% , Rated switching voltage: 230 V AC, Continuous current: 16 A,	
Qty.	10 ST	Tension-clamp connection	

PUSH IN connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOP 24VDC EMPTY	Version	
Order No.	2618740000	TERMSERIES, Relay socket, Rated control voltage: 24 V DC ±20 % ,	
GTIN (EAN)	4050118670097	Rated switching voltage: 230 V AC, Continuous current: 16 A, PUSH	
Qty.	10 ST	IN	
Type	TOP 24-230VUC EMPTY ED2	Version	
Order No.	2663110000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC ±10	
GTIN (EAN)	4050118697964	% , Rated switching voltage: 250 V AC, Continuous current: 16 A,	
Qty.	10 ST	PUSH IN	

Screw connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

Counterpart

General ordering data

Type	TOS 24-230VUC EMPTY ED2	Version
Order No.	2662950000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC ±10
GTIN (EAN)	4050118698121	%, Rated switching voltage: 250 V AC, Continuous current: 16 A,
Qty.	10 ST	Screw connection