

**ZQV 1.5N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), Plugged, orange, 17.5 A, Number of poles: 3, Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm
Order No.	<a href="#">1985480000</a>
Type	ZQV 1.5N/3
GTIN (EAN)	4050118370096
Qty.	60 items

## ZQV 1.5N/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	21.9 mm	Depth (inches)	0.8622 inch
Height	2.8 mm	Height (inches)	0.1102 inch
Width	9 mm	Width (inches)	0.3543 inch
Net weight	0.89 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

### Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes
----------------	---------	--------------------------	-----

### Dimensions

Pitch in mm (P)	3.50 mm
-----------------	---------

### General

Number of poles	3
-----------------	---

### Rating data

Rated voltage	400 V	Nominal current	17.5 A
---------------	-------	-----------------	--------

### Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V.The voltage reduced to 25 V if cut cross connection with blank cut edges are used.
---------------------	--

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		