

**PAC-HD44M-HD44F-V0-4M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |                                       |
|------------|---------------------------------------|
| Order No.  | 1989360040                            |
| Type       | <a href="#">PAC-HD44M-HD44F-V0-4M</a> |
| GTIN (EAN) | 4099986594890                         |
| Qty.       | 1 items                               |

**PAC-HD44M-HD44F-V0-4M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 880 g

**Temperatures**

Storage temperature -10...60 °C Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 4bbf2c0d-0764-4fc8-bb24-9351c28c190d

**General Data**

|                     |                      |                       |                     |
|---------------------|----------------------|-----------------------|---------------------|
| Cable length        | 4 m                  | Suitable for          | Analogue signals    |
| Basic material      | PVC                  | Cable                 | Cable LiYCY         |
| Interface connector | SUB-D HD male 44P    | Number of poles, min. | 44 poles            |
| Outer diameter      | 11,5 ± 1 mm          | Connector PLC side    | SUB-D HD female 44P |
| Wire cross-section  | 0.14 mm <sup>2</sup> |                       |                     |

**Electrical Data**

|   |            |                          |                     |
|---|------------|--------------------------|---------------------|
| Total current, max.                         | 3 A        | High voltage test        | 1 KV/1s             |
| Permissible current strength per path, max. | 1 A        | Rated voltage            | ≤ 60 Vdc ≤ 25 Vac   |
| Resistance                                  | ≤ 150 mΩ/m | Operating voltage        | ≤ 60 V DC ≤ 25 V AC |
| Capacity (wire / wires)                     | 300 pF/m   | Capacity (wire / shield) | 300 pF/m            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |