

**ZQV 1.5N/3 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 3, Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm |
| Order No.  | <a href="#">1985670000</a>   |
| Type       | ZQV 1.5N/3 RD  |
| GTIN (EAN) | 4050118370348  |
| Qty.       | 60 items   |

### Technical data

#### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

#### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 21.9 mm | Depth (inches)  | 0.8622 inch |
| Height     | 2.8 mm  | Height (inches) | 0.1102 inch |
| Width      | 9 mm    | Width (inches)  | 0.3543 inch |
| Net weight | 0.89 g  |                 |             |

#### Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

#### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

#### Material data

|                           |       |        |     |
|---------------------------|-------|--------|-----|
| Basic material            | Wemid | Colour | red |
| UL 94 flammability rating | V-0   |        |     |

#### Additional technical data

|                |         |                          |     |
|----------------|---------|--------------------------|-----|
| Type of fixing | Plugged | Explosion-tested version | Yes |
|----------------|---------|--------------------------|-----|

#### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 3.50 mm |
|-----------------|---------|

#### General

|                 |   |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

#### Rating data

|               |       |                 |        |
|---------------|-------|-----------------|--------|
| Rated voltage | 400 V | Nominal current | 17.5 A |
|---------------|-------|-----------------|--------|

#### Important note

|                     |  |
|---------------------|--|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V.The voltage reduced to 25 V if cut cross connection with blank cut edges are used. |
|---------------------|--|

#### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |