

### **ZQV 1.5N/5 RD**



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

#### **Product image**







The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

#### **General ordering data**

Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 5, Pitch in mm (P): 3.50, Insu- lated: Yes, Width: 16 mm	
<u>1985710000</u>	
ZQV 1.5N/5 RD	
4050118370256	
20 items	



## **ZQV 1.5N/5 RD**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Approvals			
ROHS	Conform		
Dimensions and weights			
Depth	21.9 mm	Depth (inches)	0.8622 inch
Height	2.8 mm	Height (inches)	0.1102 inch
Width	16 mm	Width (inches)	0.6299 inch
Net weight	1.54 g		
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
Environmental Product Com	npliance		
RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 w		
Material data			
Basic material	Wemid	Colour	red
UL 94 flammability rating	V-0	Coloui	ieu
Additional technical data		,	'
Towns of Civilian	Diverse d	Fundacion de de descritor	V
Type of fixing	Plugged	Explosion-tested version	Yes
Dimensions			
Pitch in mm (P)	3.50 mm		
General			
Number of poles	5		
Rating data			
D	400.1/		47.5 A
Rated voltage	400 V	Nominal current	17.5 A
Important note			
Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if coross connection with blank cut edges are used.		
Classifications			,
ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 3.0 ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		2, 20 00 00

Creation date 30.11.2025 09:07:36 MEZ

Catalogue status / Drawings 2