
Data sheet

# PAC-S1500-SD37-V2-3M

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

## General ordering data

| | |
|---|---|
| Version | Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm² |
| Order No. | 1991720030 |
| Type | PAC-S1500-SD37-V2-3M |
| GTIN (EAN) | 4099986595057 |
| Qty. | 1 items |

# Data sheet

## PAC-S1500-SD37-V2-3M

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 1347.58 g |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

### General Data

| | | | |
|---|---|---|---|
| Cable length | 3 m | Basic material | PVC |
| Cable | Cable LiYCY | Interface connector | SUB-D FEMALE 37P |
| Number of poles, min. | 37-pole | Outer diameter | 12.4 ± 1 mm |
| Connector PLC side | SIEMENS S71500 6ES7592-1AM00-0XB0 40P | Wire cross-section | 0.25 mm² |

### Electrical Data

| | | | |
|---|---|---|---|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 Vdc ≤ 25 Vac | Resistance | ≤ 80 mΩ/m |
| Capacity wire / wires | 300 pF/m | Capacity wire / shield | 300 pF/m |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |