

**PB-DP SUB-D ZF TERM S7**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

**General ordering data**

Version	SUB-D
Order No.	<a href="#">2004310000</a>
Type	PB-DP SUB-D ZF TERM S7
GTIN (EAN)	4050118389005
Qty.	1 items

## PB-DP SUB-D ZF TERM S7

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	16.8 mm	Depth (inches)	0.6614 inch
Height	77.7 mm	Height (inches)	3.059 inch
Width	34.7 mm	Width (inches)	1.3661 inch
Net weight	70 g		

### Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6al
REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcfaaf625

### Technical specifications for sub-D connector

Tightening torque	0.3 Nm	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Protection degree	IP30
Plugging cycles	≥ 200	Data rate	12 MBit/s
Outgoing elbow	90°	Terminating resistor available	Yes
BUS interface	D-Sub 9-pole, Pin	Plug-in connector and pin assignment	In accordance with the PROFIBUS specification
Interlock	UNC4-40	Temperature range of housing	-20...+70 °C
BUS, cable interface	Tension clamp connection	Programming interface	No

### Classifications

ETIM 8.0	EC001132	ETIM 9.0	EC001132
ETIM 10.0	EC001132	ECLASS 14.0	27-44-03-02
ECLASS 15.0	27-44-03-22		

**PB-DP SUB-D ZF TERM S7**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

Drawings

www.weidmueller.com

**Wiring diagram**

