

**SAI-M23-KBC-L-0.75/2.50**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

**General ordering data**

Version	Sensor/Actuator plug-in connector, Crimp contact
Order No.	<a href="#">1995820000</a>
Type	SAI-M23-KBC-L-0.75/2.50
GTIN (EAN)	403224892568 1
Qty.	50 items

**SAI-M23-KBC-L-0.75/2.50**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E344862

**Dimensions and weights**

Length	23.6 mm	Length (inches)	0.9291 inch
Net weight	0.94 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	7baf363e-d867-435e-844e-c01f32ebf146

**Settings re. SAI M23 crimping tool**

Settings regarding SAI M23 crimping tool	Crimping Tool	1		
	Locator position	8		
	Crimp contact	Crimp socket power 2 mm		
	Crimping mandrel adjustment acc. to mm <sup>2</sup>	Wire cross-section	0.75 mm <sup>2</sup>	
		Crimping mandrel adjustment	1.3	
	Wire cross-section	1.00 mm <sup>2</sup>		
		Crimping mandrel adjustment	1.4	
	Wire cross-section	1.50 mm <sup>2</sup>		
		Crimping mandrel adjustment	1.55	
Wire cross-section	2.50 mm <sup>2</sup>			
	Crimping mandrel adjustment	1.7		

**Technical data customisable plug-in connectors**

Contact surface	Gold-plated	Type of connection	Crimp connection
Insulation resistance	> 1010 Ω	Contact material	Copper-Zinc alloy
Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	0.75 mm <sup>2</sup>
Plugging cycles	> 1000	Gender of contact	Female

**Classifications**

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Drawing

