


## HDC XX5E01 MOXXXXX-0100

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Compact

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

### General ordering data

|            |                            |
|------------|----------------------------|
| Version    | Data use                   |
| Order No.  | <a href="#">2003890100</a> |
| Type       | HDC XX5E01 MOXXXXX-0100    |
| GTIN (EAN) | 4050118464481              |
| Qty.       | 1 items                    |

## HDC XX5E01 MOXXXXX-0100

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 73.04 g |
|------------|---------|

## Temperatures

|                   |                  |
|-------------------|------------------|
| Limit temperature | -30 °C ... 90 °C |
|-------------------|------------------|

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5 |

## General data

|                       |            |                       |           |
|-----------------------|------------|-----------------------|-----------|
| Number of poles       | 4          | Cable length          | 1 m       |
| Coding                | D-coded    | Contact surface       | Au (Gold) |
| Transmission rate     | 100 MBit/s | Insulation resistance | ≥ 108 Ω   |
| Category              | Cat. 5e    | Nominal voltage       | 250 V     |
| Nominal current       | 4 A        | Plugging cycles       | ≥ 100     |
| Type                  | Pin        | Pollution severity    | 2         |
| Opposite side version | open       | Module side version   | Male      |

## Cable technical specifications

|                  |                             |        |
|------------------|-----------------------------|--------|
| Cable length     | 1 m                         |        |
| Sheathing colour | green                       |        |
| Shielded         | Yes                         |        |
| Halogen          | No, halogen-free            |        |
| Insulation       | PE                          |        |
| Sheath material  | PUR                         |        |
| Colour coding    | white, yellow, blue, orange |        |
| Outside diameter | Diameter                    | 6.5 mm |
|                  | Signs                       | ±      |
|                  | Tolerance                   | 0.2    |
| Outside diameter | 6.5 mm ± 0.2                |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-07 |
| ECLASS 15.0 | 27-06-03-07 |             |             |

**HDC XX5E01 MOXXXXX-0100**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

---

---

|        | M12 |
|--------|-----|
| yellow | 1   |
| white  | 2   |
| orange | 3   |
| blue   | 4   |

---

---