

## WM 3/6 5.0-8.0 MM WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Un-detachable: WM

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm<sup>2</sup> to 16mm<sup>2</sup>. Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

### Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

### General ordering data

Version	WM, Conductor and cable markers, 5 - 8 mm, 17 x 10 mm, white
Order No.	<a href="#">2006390000</a>
Type	WM 3/6 5.0-8.0 MM WS
GTIN (EAN)	4050118390469
Qty.	2000 items

## WM 3/6 5.0-8.0 MM WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	17 mm	Height (inches)	0.6693 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	0.16 g		

### Temperatures

Operating temperature range	-40...150 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	150 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	Version	halogen-free
Width	10 mm	UL 94 flammability rating	HB
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	No
Basic material	Polyester	Printed characters	without
Size of labelling field	7 x 10 mm	compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>
Operating temperature range	-40...150 °C		

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>	Conductor O.D., max.	8 mm
Conductor O.D., min.	5 mm	Text field width	7 mm
Text field height	10 mm	Conductor O.D.	5 - 8 mm
Cross-section for connected wire	4 - 16 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

