

## WM 0/6 1.0-2.0 MM GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Un-detachable: WM

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm<sup>2</sup> to 16mm<sup>2</sup>. Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

### Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

### General ordering data

|            |  |
|------------|--|
| Version    | WM, Conductor and cable markers, 1 - 2 mm, 17 x 3.5 mm, yellow |
| Order No.  | <a href="#">2006410000</a>                                     |
| Type       | WM 0/6 1.0-2.0 MM GE   |
| GTIN (EAN) | 4050118390438  |
| Qty.       | 2000 items   |

## WM 0/6 1.0-2.0 MM GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.5 mm | Depth (inches)  | 0.0197 inch |
| Height     | 17 mm  | Height (inches) | 0.6693 inch |
| Width      | 3.5 mm | Width (inches)  | 0.1378 inch |
| Net weight | 0.06 g |                 |             |

### Temperatures

|                                  |              |                                  |        |
|----------------------------------|--------------|----------------------------------|--------|
| Operating temperature range      | -40...150 °C | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 150 °C       |                                  |        |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |              |                                   |  |
|-----------------------------------|--------------|-----------------------------------|--|
| Type of printing                  | neutral      | Version                           | halogen-free   |
| Width                             | 3.5 mm       | UL 94 flammability rating         | HB   |
| Operating temperature range, max. | 150 °C       | Operating temperature range, min. | -40 °C   |
| Colour                            | yellow       | Halogen                           | No   |
| Basic material                    | Polyester    | Printed characters                | without  |
| Size of labelling field           | 7 x 3.5 mm   | compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> |
| Operating temperature range       | -40...150 °C |                                   |  |

### Conductor and cable markers

|                                  |                            |                               |                      |
|----------------------------------|----------------------------|-------------------------------|----------------------|
| Halogen                          | No                         | Conductor cross-section, max. | 0.75 mm <sup>2</sup> |
| Conductor cross-section, min.    | 0.5 mm <sup>2</sup>        | Conductor O.D., max.          | 2 mm                 |
| Conductor O.D., min.             | 1 mm                       | Text field width              | 7 mm                 |
| Text field height                | 2.5 mm                     | Conductor O.D.                | 1 - 2 mm             |
| Cross-section for connected wire | 0.5 - 0.75 mm <sup>2</sup> |                               |                      |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

