

**WS 8/6 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**WS/ DEK**

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

|            |   |
|------------|---|
| Version    | WS, Terminal marker, 8 x 6 mm, Weidmueller, white |
| Order No.  | <a href="#">2007160000</a>                        |
| Type       | WS 8/6 MM WS                                      |
| GTIN (EAN) | 4050118391879                                     |
| Qty.       | 600 items   |

## WS 8/6 MM WS

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

|      |         |
|------|---------|
| RoHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 8 mm   | Height (inches) | 0.315 inch  |
| Width      | 6 mm   | Width (inches)  | 0.2362 inch |
| Net weight | 0.12 g |                 |             |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -50...90 °C |
|-----------------------------|-------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                   |              |                                   |  |
|-----------------------------------|--------------|-----------------------------------|--|
| Version                           | halogen-free | Width                             | 6 mm   |
| UL 94 flammability rating         | V-2          | Operating temperature range, max. | 90 °C  |
| Operating temperature range, min. | -50 °C       | Colour                            | white  |
| Halogen                           | No           | Basic material                    | PC-ABS, TPU  |
| Printed characters                | neutral      | compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> |
| Operating temperature range       | -50...90 °C  | Application/manufacturer          | Weidmüller   |
| Number per roll                   | 600          |                                   |  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**WS 8/6 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Example of use**

**WS 8/6 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**


|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM-TB 25/360 SW     | Version    |
| Order No.  | <a href="#">2005090000</a> | Ink ribbon |
| GTIN (EAN) | 4050118390216              |            |
| Qty.       | 1 ST                       |            |

**THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |         |
|------------|----------------------------|---------|
| Type       | MULTIMARK ROLLER TB        | Version |
| Order No.  | <a href="#">2438500000</a> |         |
| GTIN (EAN) | 4050118498721              |         |
| Qty.       | 1 ST                       |         |

**THM MULTIMARK PLUS**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |         |
|------------|----------------------------|---------|
| Type       | MULTIMARK PLUS ROLLER TB   | Version |
| Order No.  | <a href="#">2661600000</a> |         |
| GTIN (EAN) | 4050118681246              |         |
| Qty.       | 1 ST                       |         |