

## WS 12/3.5 MM WS


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

#### Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

### General ordering data

Version	WS, Terminal marker, 12 x 3.5 mm, Weidmueller, white
Order No.	<a href="#">2007180000</a>
Type	WS 12/3.5 MM WS
GTIN (EAN)	4050118392203
Qty.	1000 items

**WS 12/3.5 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	12 mm	Height (inches)	0.4724 inch
Width	3.5 mm	Width (inches)	0.1378 inch
Net weight	0.06 g		

**Temperatures**

Operating temperature range -50...90 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Version	halogen-free	Width	3.5 mm
UL 94 flammability rating	V-2	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	Colour	white
Halogen	No	Basic material	PC-ABS, TPU
Printed characters	neutral	compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>
Operating temperature range	-50...90 °C	Application/manufacturer	Weidmueller

**Classifications**

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

**Example of use**

