

**IE-PS-M12X-P-AWG22/27FH****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

**General ordering data**

Version	Plugs prefabricated to customer spec., M12, IDC, Cat.6A / Class EA (ISO/IEC 11801 2010), IP67 plugged
Order No.	<a href="#">2007500000</a>
Type	IE-PS-M12X-P-AWG22/27FH
GTIN (EAN)	4050118392937
Qty.	1 items

## IE-PS-M12X-P-AWG22/27FH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E471884

## Dimensions and weights

Net weight	0 g
------------	-----

## Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
Installation temperature		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

## Technical data customisable plug-in connectors

Number of poles	8	Coding	X-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Insulation resistance	100 MΩ	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact material	Brass, tinned	Nominal voltage	50 V
Protection degree	IP67 plugged	Plugging cycles	≥ 100
Gender of contact	Male	Shield connection	Yes, screwed

## General Info

Number of poles	8	Connection 1	M12
Connection 2	IDC	Housing main material	Zinc diecast
Insulation cross-section, min.	0.9 mm	Insulation cross-section, max.	1.6 mm
Category	Cat.6A / Class EA (ISO/IEC 11801 2010)	Connection thread	M12
Contact material	Brass, tinned	Contact surface	Gold-plated
Wire connection diameter, solid, min.	0.51 mm	Connection diameter, solid	0.51...0.64 mm
Wire connection diameter, solid, max.	0.64 mm	Conductor connection cross-section, solid (AWG)	AWG 24/1...AWG 22/1
Wire cross-section, solid, min. (AWG)	AWG 24/1	Connection diameter, flexible	0.46...0.76 mm
Wire cross-section, solid, max. (AWG)	AWG 22/1	Conductor connection cross-section, flexible (AWG)	AWG 27/7...AWG 22/7
Wire connection diameter, flexible, min.	0.46 mm	Wire connection diameter, flexible, max.	0.76 mm
Wire cross-section, finely stranded, min. (AWG)	AWG 27/7	Wire cross-section, finely stranded, max. (AWG)	AWG 22/7
Conductor connection diameter, very finely stranded, min.	0.61 mm	Conductor connection cross-section, extremely flexible	0.61...0.78 mm, Approval of the cable by Weidmüller necessary

## IE-PS-M12X-P-AWG22/27FH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Conductor connection diameter, very finely stranded, max.	0.78 mm	Conductor connection cross-section, very finely stranded, min. (AWG)	AWG 26
Conductor connection cross-section, extremely flexible (AWG)	AWG 26...AWG 22, Approval of the cable by Weidmüller necessary	Conductor connection cross-section, very finely stranded, max. (AWG)	AWG 22
Note, very finely stranded line connection	Approval of the cable by Weidmüller necessary	Sheath diameter, min.	5.5 mm
Sheath diameter, max.	9 mm	Contact holder materials	PA
Shielding material	Nickel silver	Shielding	360° all-round enclosure
Protection degree	IP67 plugged	Plugging cycles	≥ 100

## Electrical properties

Dielectric strength, contact / shield	≥ 500 V DC	Dielectric strength, contact / contact	≥ 500 V DC
Volume resistance	<10 mΩ	Insulation resistance	100 MΩ
Nominal voltage	50 V	PoE / PoE+	conforming to IEEE 802.3at

## General standards

Connector standard	IEC 61076-2-109	Certificate no. (cULus)	E471884
--------------------	-----------------	-------------------------	---------

## Standards

Connector standard	IEC 61076-2-109
--------------------	-----------------

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16
ECLASS 13.0	27-44-01-02	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

## IE-PS-M12X-P-AWG22/27FH

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Drawing

