

**THM WO 24.5/100 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 8 - 23 mm, 25.4 x 100 mm, white
Order No.	<a href="#">2004970000</a>
Type	THM WO 24.5/100 WS
GTIN (EAN)	4050118415391
Qty.	2000 items

## THM WO 24.5/100 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	0.36 g		

## Temperatures

Operating temperature range -40...150 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## General data

Adhesive	Polyacrylate adhesive	
Type of printing	neutral	
Width	100 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	24.5 x 25 mm	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...150 °C	
Number per roll	2000	

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	23 mm
Conductor O.D., min.	8 mm	Text field width	24.5 mm
Text field height	25 mm	Conductor O.D.	8 - 23 mm
Cross-section for connected wire	0.75 - 120 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		