

WM 2/21 3.5-5.0 MM WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Un-detachable: WM

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm² to 16mm². Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

| | |
|------------|---|
| Version | WM, Conductor and cable markers, 3.5 - 5 mm, 32 x 6.4 mm, white |
| Order No. | 2006050000 |
| Type | WM 2/21 3.5-5.0 MM WS |
| GTIN (EAN) | 4050118390407 |
| Qty. | 2000 items |

WM 2/21 3.5-5.0 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.5 mm | Depth (inches) | 0.0197 inch |
| Height | 32 mm | Height (inches) | 1.2598 inch |
| Width | 6.4 mm | Width (inches) | 0.252 inch |
| Net weight | 0.17 g | | |

Temperatures

| | | | |
|----------------------------------|--------------|----------------------------------|--------|
| Operating temperature range | -40...150 °C | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 150 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|--|
| Type of printing | neutral | Version | halogen-free |
| Width | 6.4 mm | UL 94 flammability rating | HB |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Colour | white | Halogen | No |
| Basic material | Polyester | Printed characters | without |
| Size of labelling field | 22 x 6.4 mm | compatible printer | THM MULTIMARK , THM MULTIMARK PLUS |
| Operating temperature range | -40...150 °C | | |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | No | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 2.5 mm ² | Conductor O.D., max. | 5 mm |
| Conductor O.D., min. | 3.5 mm | Text field width | 22 mm |
| Text field height | 6.4 mm | Conductor O.D. | 3.5 - 5 mm |
| Cross-section for connected wire | 2.5 - 4 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

WM 2/21 3.5-5.0 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM 76/360 SW | Version | |
| Order No. | 2005080000 | Ink ribbon | |
| GTIN (EAN) | 4050118389951 | | |
| Qty. | 1 ST | | |

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER 115 | Version | |
| Order No. | 1357420000 | | |
| GTIN (EAN) | 4050118160314 | | |
| Qty. | 1 ST | | |

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK PLUS ROLLER 1... | Version | |
| Order No. | 2672590000 | | |
| GTIN (EAN) | 4050118708097 | | |
| Qty. | 1 ST | | |