WM 2/6 3.5-5.0 MM GE



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Un-detachable: WM

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm^2 to 16mm^2 . Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- · Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

Version	WM, Conductor and cable markers, 3.5 - 5 mm,	
	17 x 6.4 mm, yellow	
Order No.	2006450000	
Туре	WM 2/6 3.5-5.0 MM GE	
GTIN (EAN)	4050118390155	
Qty.	2000 items	

1

Catalogue status / Drawings



WM 2/6 3.5-5.0 MM GE



Weidmüller Interface GmbH & Co. KG

27-28-11-02

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals					
ROHS	Conform				
Dimensions and weights					
Depth	0.5 mm	Depth (inches)	0.0197 inch		
Height	17 mm	Height (inches)	0.6693 inch		
Width	6.4 mm	Width (inches)	0.252 inch		
Net weight	0.1 g				
Temperatures					
Operating temperature range	-40150 °C	Continuous operating temp., min.	-40 °C		
Continuous operating temp., max.	150 °C	gonunaeus sporuung temp., min.	10 0		
Environmental Product Com	nlianaa		<u> </u>		
Environmental Froduct Com	pnance				
RoHS Compliance Status	Compliant without exemption				
REACH SVHC	No SVHC above 0.1 wt%				
General data Type of printing	neutral	Version	halogen-free		
Width	6.4 mm	UL 94 flammability rating	HB		
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C		
Colour	yellow	Halogen	No		
Basic material	Polyester	Printed characters	without		
Size of labelling field	7 x 6.4 mm	compatible printer	THM MULTIMARK, THN MULTIMARK PLUS		
Operating temperature range	-40150 °C				
Conductor and cable marker	's				
Halogen	No	Conductor cross-section, max.	4 mm²		
Conductor cross-section, min.	2.5 mm ²	Conductor O.D., max.	5 mm		
Conductor O.D., min.	3.5 mm	Text field width	7 mm		
Text field height	6.4 mm	Conductor O.D.	3.5 - 5 mm		
Cross-section for connected wire	2.5 - 4 mm²				
Classifications					
ETIM 6.0	EC001530	ETIM 7.0	EC001530		
ETIM 8.0	EC001530	ETIM 9.0	EC001530		
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01		
ECLASS 9.1	27-40-04-01	ECLASS 3.0 ECLASS 10.0	27-40-04-01		
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02		
ECLASS 12.0	27 20 11 02	ECLASS 14.0	27 20 11 02		

ECLASS 13.0

ECLASS 15.0

Catalogue status / Drawings 2

ECLASS 14.0

27-28-11-02

27-28-11-02

Data sheet

WM 2/6 3.5-5.0 MM GE



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings

