

**KTB GP XX2615 AB S4 PE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 254 mm, Width: 117 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">2023160000</a>
Type	KTB GP XX2615 AB S4 PE
GTIN (EAN)	4050118403794
Qty.	1 items

**KTB GP XX2615 AB S4 PE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	3 mm	Depth (inches)	0.1181 inch
Height	254 mm	Height (inches)	10 inch
Width	117 mm	Width (inches)	4.6063 inch
Net weight	725 g		

**Temperatures**

Operating temperature	
-----------------------	--

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Material thickness	3 mm	Installation advice	Screw mounting
Surface finish	electropolished	Basic material	Stainless steel 1.4404
Integral fixing	Screwed	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	top, Bottom	Flange plate	Yes
Areas of use	Transportation, Explosive risk zone		

**General information on accessories**

Material thickness	3 mm	Solder eyelet hole diameter (D)	7 mm
Surface finish	electropolished	Basic material	Stainless steel 1.4404

**Housing earth**

Flange plate earthing	M6 x 15
-----------------------	---------

**Classifications**

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		