

## KTB GP 765020 AB S4 PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

### General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 498 mm, Width: 167 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">2024100000</a>
Type	KTB GP 765020 AB S4 PE
GTIN (EAN)	4050118404531
Qty.	1 items
Delivery status	Discontinued
Available until	2024-10-31T00:00:00+01:00
Alternative product	<a href="#">KTB GP XX5020V AB S4 PE</a>

Creation date 05.03.2026 04:54:56 MEZ

Catalogue status / Drawings

**KTB GP 765020 AB S4 PE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	3 mm	Depth (inches)	0.1181 inch
Height	498 mm	Height (inches)	19.6063 inch
Width	167 mm	Width (inches)	6.5748 inch
Net weight	1950 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Material thickness	3 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	top, Bottom		

**General information on accessories**

Material thickness	3 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404		

**Housing earth**

Flange plate earthing M6 x 15

**Classifications**

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		