

KTB GP XX6120 AB S4 PE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

| | |
|------------|---|
| Version | Klippon TB (Terminal Box), flange plate, straight, Height: 600 mm, Width: 167 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404, electropolished, silver |
| Order No. | 2024470000 |
| Type | KTB GP XX6120 AB S4 PE |
| GTIN (EAN) | 4050118404418 |
| Qty. | 1 items |

KTB GP XX6120 AB S4 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 3 mm | Depth (inches) | 0.1181 inch |
| Height | 600 mm | Height (inches) | 23.622 inch |
| Width | 167 mm | Width (inches) | 6.5748 inch |
| Net weight | 2405 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

| | | | |
|--------------------|-------------------------------------|-----------------------|--------------------------|
| Material thickness | 3 mm | Installation advice | Screw mounting |
| Surface finish | electropolished | Basic material | Stainless steel 1.4404 |
| Integral fixing | Screwed | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Gland plates | top, Bottom | Flange plate | Yes |
| Areas of use | Transportation, Explosive risk zone | | |

General information on accessories

| | | | |
|--------------------|-----------------|---------------------------------|------------------------|
| Material thickness | 3 mm | Solder eyelet hole diameter (D) | 7 mm |
| Surface finish | electropolished | Basic material | Stainless steel 1.4404 |

Housing earth

Flange plate earthing M6 x 15

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000211 | ETIM 9.0 | EC000211 |
| ETIM 10.0 | EC000211 | ECLASS 14.0 | 27-14-24-21 |
| ECLASS 15.0 | 27-14-24-21 | | |