

## SFX 10/60 S MC NE GE V0


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	SlimFix X, Conductor and cable markers, 7 - 40 mm, 60 x 13.62 mm, yellow
Order No.	<a href="#">2009900000</a>
Type	SFX 10/60 S MC NE GE V0
GTIN (EAN)	4050118396294
Qty.	50 items

## SFX 10/60 S MC NE GE V0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	13.62 mm	Width (inches)	0.5362 inch
Net weight	2.3 g		

### Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.015 kg CO2 eq.	

### General data

Version	Installation with cable ties		
Width	13.62 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	120 °C		
Operating temperature range, min.	-50 °C		
Colour	yellow		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	60 x 9.5 mm		
compatible printer	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-50...120 °C		

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	40 mm
Conductor O.D., min.	7 mm	Conductor O.D.	7 - 40 mm
Cross-section for connected wire	16 - 500 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		