

## IE-FM6D2UE0310MSDSSDSX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5, 6 and 14
- consistently Cat. 6A with STEADYTEC® technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

### General ordering data

Version	Dragline cable, SC IP 67 bayonet V01 metal, SC IP 67 bayonet V01 metal, 62.5 µm, PUR, 310 m
Order No.	<a href="#">2035373100</a>
Type	IE-FM6D2UE0310MSDSSDSX
GTIN (EAN)	4050118407693
Qty.	1 items

**IE-FM6D2UE0310MSDSSDSX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Length	310 m	Length (inches)	12204.7244 inch
Net weight	8190 g		

**Temperatures**

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

**Fibre-optic**

Fibre type	GOF, Multimode, OM1	Attenuation	2.7 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm
Bandwidth	200 MHz*km at 850 nm, 500 MHz*km at 1300 nm		

**Cable structure**

Sheath diameter	6 mm	Sheathing colour	black
Material sheath	PUR	Cable layout	Break-out dragline
Primary coating	245.00 µm	Core diameter	62.5 µm

**Mechanical and material properties of cable**

Min. bending radius, repetitive	77 mm	Min. bending radius, once only	25 mm
Bending cycles	100,000		

**Classifications**

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		