

KTB GP 62XX20 CD S4 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 564 mm, Width: 167 mm, Depth: 3 mm, Gland plates: left, right, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	2023930000
Type	KTB GP 62XX20 CD S4 PE
GTIN (EAN)	4050118404319
Qty.	1 items
Delivery status	Discontinued
Available until	2024-10-31T00:00:00+01:00
Alternative product	KTB GP 62XX20 CD S4 PE

KTB GP 62XX20 CD S4 PE
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Technical data
Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	564 mm	Height (inches)	22.2047 inch
Width	167 mm	Width (inches)	6.5748 inch
Net weight	2230 g		

Temperatures

Operating temperature	
-----------------------	--

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	3 mm	Installation advice	Screw mounting
Surface finish	electropolished	Basic material	Stainless steel 1.4404
Integral fixing	Screwed	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	left, right	Flange plate	Yes
Areas of use	Transportation, Explosive risk zone		

General information on accessories

Material thickness	3 mm	Solder eyelet hole diameter (D)	7 mm
Surface finish	electropolished	Basic material	Stainless steel 1.4404

Housing earth

Flange plate earthing	M6 x 15
-----------------------	---------

Classifications

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		