

**SAIL-M12G-S-3.0P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

|            |                                                                                                                                                         |
|------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Power cable, One end without connector, M12, Number of poles : 4 (3 + PE), 3 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">2050230300</a>                                                                                                                              |
| Type       | SAIL-M12G-S-3.0P                                                                                                                                        |
| GTIN (EAN) | 4050118441130                                                                                                                                           |
| Qty.       | 1 items                                                                                                                                                 |

## SAIL-M12G-S-3.0P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E310075

## Dimensions and weights

Net weight 200 g

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

## Technical specifications for cable

|                                                |                                  |                               |                      |
|------------------------------------------------|----------------------------------|-------------------------------|----------------------|
| Cable length                                   | 3 m                              | Sheathing colour              | black                |
| Resistance to oils                             | Yes                              | PE function                   | Yes                  |
| Suitable for cable carriers                    | Yes                              | Core cross-section            | 1.5 mm <sup>2</sup>  |
| Number of wires                                | 4                                | Shielded                      | No                   |
| Halogen                                        | No                               | Insulation                    | PP                   |
| Acceleration                                   | 5 m/s <sup>2</sup>               | Bending radius, min., moving  | 7.5 x cable diameter |
| Bending radius, min., stationary               | 4 x cable diameter               | Bending cycles                | 10 Mio               |
| Resistance to spread of flame                  | in accordance with IEC 60332-1-2 | Speed                         | 5 m/s                |
| Sheath material                                | PUR                              | Cable length configurable     | No                   |
| Outer cladding in accordance with UL AWM style | 20234 (80 °C / 1000 V)           | Type is hybrid cable          | No                   |
| Irradiation crosslinked                        | No                               | Welding spark resistance      | No                   |
| Colour coding                                  | brown, black, grey, Green/yellow | Temperature range, stationary | -50...80 °C          |
| Resistant to welding beads                     | No                               | Temperature range, moving     | -40...80 °C          |
| Number of poles                                | 4 (3 + PE)                       |                               |                      |

## General technical data

|                        |                    |                              |                                   |
|------------------------|--------------------|------------------------------|-----------------------------------|
| Coding                 | S-coded            | Connection thread            | M12                               |
| Contact surface        | Gold-plated        | LED                          | No                                |
| Version                | pin, straight      | Housing main material        | PUR                               |
| Insulation resistance  | 108 Ω              | Contact material             | CuZn                              |
| Nominal voltage        | 600 V              | Nominal current              | 12 A                              |
| AF size                | 13 mm              | Protection degree            | IP65, IP67, IP68, when screwed in |
| Plugging cycles        | ≥ 100              | Pollution severity           | 3                                 |
| Threaded ring material | Nickel-plated CuZn | Temperature range of housing | -30...+90 °C                      |
| Tightening torque      | M12: 1.0 Nm        |                              |                                   |

## Electrical properties

|                       |       |                 |       |
|-----------------------|-------|-----------------|-------|
| Insulation resistance | 108 Ω | Nominal voltage | 600 V |
|-----------------------|-------|-----------------|-------|

**SAIL-M12G-S-3.0P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data****General standards**

|                    |                 |                         |         |
|--------------------|-----------------|-------------------------|---------|
| Connector standard | IEC 61076-2-111 | Certificate no. (cULus) | E310075 |
|--------------------|-----------------|-------------------------|---------|

**Standards**

|                    |                 |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-111 |
|--------------------|-----------------|

**Plug, left**

|           |                                                                            |
|-----------|----------------------------------------------------------------------------|
| Plug left | M12, S-coded, Number of poles: 4, male contact, straight, plug, unshielded |
|-----------|----------------------------------------------------------------------------|

**Plug, right**


|            |                    |
|------------|--------------------|
| Plug right | Free conductor end |
|------------|--------------------|

**Classifications**


|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ETIM 10.0   | EC001855    | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 |             |             |

## Drawings


### Dimensioned drawing



### Pole scheme



### Wiring diagram



### The ideal tool: Screwty® with torque function

