

VP M32 EX SI 7J

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK EX 7J (Ex blanking plug, plastic, 7J), Blanking plug, in closed state, M 32, 15 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	2066750000
Type	VP M32 EX SI 7J
GTIN (EAN)	4050118415445
Qty.	100 items

VP M32 EX SI 7J

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	22.8 mm	Height (inches)	0.8976 inch
Length	22.8 mm	Length (inches)	0.8976 inch
Diameter	32 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	14 mm	Net weight	11.87 g

Temperatures

Operating temperature -60 °C...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

Identification	Ex eb IIC Gb, Ex tb IIIC Db IP66/68	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (INMETRO)	TAE00003WV	Certificate no. cable gland (IECEX)	IECEX IMQ 13.0003X
Approval conditions	ATEX, IECEX		

General information

O-Ring	Silicone	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Silicone	Yes	UL 94 flammability rating	HB
Operating temperature range, max.	70 °C	Operating temperature range, min.	-60 °C
Pitch of thread	1.5 mm	Halogen	No
Standards	IEC 60079-0, EN 60079-0, IEC 60079-7, EN 60079-7, EN 60079-31, IEC 60079-31	Impact resistance	7 joules in acc. with IEC60079-0
AF size 1	36 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Basic material	Polyamide 6	Diameter of sealing ring	32.00 mm
Sealing	Silicone	External thread	M 32
Length of thread	15 mm	Torque for lock nut, min.	3.80 Nm
Torque for connecting adapter, max.	4.00 Nm	Torque for connecting adapter, min.	4.00 Nm
Explosion protection type	Improved safety Ex e	Installation guidelines	See assembly instructions
Torque for lock nut, max.	4.00 Nm		

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

VP M32 EX SI 7J

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M32 MS	Version	
Order No.	1737020000	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated	
GTIN (EAN)	4008190956493		
Qty.	100 ST		