

VP M50 EX SI 7J**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK EX 7J (Ex blanking plug, plastic, 7J), Blanking plug, in closed state, M 50, 18 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	2066770000
Type	VP M50 EX SI 7J
GTIN (EAN)	4050118415469
Qty.	20 items

VP M50 EX SI 7J

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	27.5 mm	Height (inches)	1.0827 inch
Length	27.5 mm	Length (inches)	1.0827 inch
Diameter	50 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	17 mm	Net weight	30.8 g

Temperatures

Operating temperature -60 °C...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

Identification	Ex eb IIC Gb, Ex tb IIIC Db IP66/68	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (INMETRO)	TAE00003WV	Certificate no. cable gland (IECEX)	IECEX IMQ 13.0003X
Approval conditions	ATEX, IECEX		

General information

O-Ring	Silicone	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Silicone	Yes	UL 94 flammability rating	HB
Operating temperature range, max.	70 °C	Operating temperature range, min.	-60 °C
Pitch of thread	1.5 mm	Halogen	No
Standards	IEC 60079-0, EN 60079-0, IEC 60079-7, EN 60079-7, EN 60079-31, IEC 60079-31	Impact resistance	7 joules in acc. with IEC60079-0
AF size 1	55 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Basic material	Polyamide 6	Diameter of sealing ring	50.00 mm
Sealing	Silicone	External thread	M 50
Length of thread	18 mm	Torque for lock nut, min.	7.80 Nm
Torque for connecting adapter, max.	8.00 Nm	Torque for connecting adapter, min.	8.00 Nm
Explosion protection type	Improved safety Ex e	Installation guidelines	See assembly instructions
Torque for lock nut, max.	8.00 Nm		

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		